

# DF14N

Fuse carrier TeSys DF, Neutral 50A, fuse size 14x51 mm, with tubular link



## Main

Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DF14
Device composition	Tubular link for locked in Neutral pole
Poles description	1N
Fuse size	14 x 51 mm
Fuse type	, gG , aM
Control type	Toggle
[Ue] rated operational voltage	690 V AC 690 V DC
[Ie] rated operational current	50 A
[Ui] rated insulation voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ipk] rated peak withstand current	15 kA with tubular links conforming to IEC 60269-1
Short-circuit withstand	120 KA 400 V conforming to IEC 60947-3 120 KA 500 V conforming to IEC 60947-3 80 kA 690 V conforming to IEC 60947-3

## Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1
Product certifications	IEC UL recognized when associated with a phase fuse carrier CSA EAC
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical (tolerance: +/- 23°)
Connections - terminals	Screw clamp terminals 1 cable(s) 2.5...25 mm <sup>2</sup> rigid Screw clamp terminals 2 cable(s) 2.5...10 mm <sup>2</sup> rigid Screw clamp terminals 1 cable(s) 2.5...25 mm <sup>2</sup> flexible with or without Screw clamp terminals 2 cable(s) 2.5...10 mm <sup>2</sup> flexible with or without
Tightening torque	3.5 N.m
Height	110.8 mm
Width	26.5 mm
Depth	76.5 mm
Net weight	0.150 kg
Quantity per set	Set of 6

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	-40...80 °C
Ambient air temperature for operation	-20...60 °C with derating above 20°C
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH
Fire resistance	960 °C conforming to IEC 60695-2-1
Compatibility code	DF14

## Packing Units

Package 1 Weight	137 g
Package 2 Weight	827 g
Package 3 Weight	10.504 kg

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------