



Commercial status
End of Commercialisation :

⚠ End of Commercialisation

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	CD with software Telephone cable User manual
Max runtime	7 Min
Performance multiplier	1
Number of tare power	7 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS
Value multiplier	1

Physical

Cable length	1.83 M
Colour	Black
Depth	31.1 Cm
Height	8.9 Cm
Mounting preference	No preference
Net weight	6.93 Kg
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Width	22.4 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	BS1363A British
Input voltage limits	180...266 V
Maximum input current	10 A
Switching current capacity	10 A
Input voltage	230 V

Output

Rated power in W	405 W
Maximum configurable power in W	405 W
Output frequency	47...63 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
UPS type	Standby
Wave type	Stepped approximation to a sinewave
Nb of power socket outlets	4 BS 1363 4 BS 1363 surge
Output voltage tolerance	+/- 5% static and 100% load step
Curve equation	Efficiency
Curve fixed loss	0.0107
Curve load maximum	100 %
Curve load minimum	2 %
Curve proportional loss	0
Curve square loss	0.0017
Curve X-axis maximum	100 %
Curve test cond ID	Curve fit of data measured in accordance with the ENERGY STAR Test Method for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 230V/50Hz electrical input and balanced resistive load (PF = 1.0) output.
Curve X-axis minimum	0 %
Curve X-axis title	Load
Curve X-axis units	Percentage
Curve Y-axis maximum	100 %
Curve Y-axis minimum	50 %
Curve Y-axis title	Efficiency
Curve Y-axis units	Percentage
Graph display	1
Output voltage	230 V
Maximum configurable power in VA	700 VA
Rated power in VA	700 VA
Transfer time	6 ms typical : 10 ms maximum

Conformance

Product certifications	CE
Equipment protection policy	Lifetime : 50000 GBP

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...30000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...9144.00 M
Acoustic level	40 dBA
Show note OP temperature	No

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	16 H
Liquid value	0
Battery curve	C
Battery charger power	5 W rated
Battery power in VAH	86 VAh runtime
Battery life	3...5 Year(S)
Extended runtime	0

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
---------------	--

Surge Protection and Filtering

Surge energy rate	310 J
Noise suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data line protection	RJ45 analog phone line for phone/fax/modem/DSL RJ45 network line - 10/100 base-T Ethernet

Packing Units

Package 1 Weight	7.84 Kg
Package 1 Height	12.7 Cm
Package 1 width	27.9 Cm
Package 1 Length	40 Cm
SCC14	10731304268342
Number of Units in Package 2	2
Package 2 Weight	16.33 Kg
Package 2 Length	323.85 Mm
Number of Units in Package 3	48
Package 3 Weight	636.36 Kg
Package 3 Length	121.92 Cm
Pallet unit layers	20
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	---

Product Life Status : **End of commerc. announced**

BE700G-UK may be replaced by any of the following products:



BE850G2-UK

APC Back-UPS 850VA, 230V, USB Type-C and A charging ports

Qty 1

Reason for Substitution: End of life | Substitution date: 15 Dec 2020 | Linking to group 1
