



182.72.104.66PWKR..-2RSKurvenrollen

Stud type track rollers

PWKR72-2RS-XL (Series PWKR..-2RS)

with axial guidance, full complement cylindrical roller set,
lip seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

D	72 mm
d1	24 mm Tolerance: h7
B	80 mm
B1 max	30,6 mm
B2	49,5 mm
B3	11 mm
C	28 mm
C1	1,3 mm
d2	44 mm
d3	4 mm
G	M24x1,5
lG	25 mm
rmin	1,1 mm
W	14 mm Nominal dimension for hexagonal socket
m	1020 g Mass
MA	220 Nm Nut tightening torque
Cr w	38500 N Effective dynamic load rating as track roller (radial)
Cor w	54000 N Effective static load rating as track roller (radial)

F_r per	39000 N	Permissible dynamic radial load
F_{0r} per	54000 N	Permissible static radial load
C_{urw}	6900 N	Fatigue limit load
n_D G	2200 1/min	Speed (with continuous operation and grease lubrication)
	NIPA3X9,5	Drive fit lubrication nipple Drive fit lubrication nipples are supplied loose. Only these lubrication nipples should be used.
AP	AP14	Suitable central lubrication adapter for connection to a central lubrication system

