

Demolition hammer XGT®

HM001G

40V max • SDS-MAX • 18 mm • 9.4 J

Cordless XGT® Demolition Hammer for professionals.

High power and compact design. Soft start suppresses start-up reaction for more control and better accuracy. Rubberised ergonomic soft grip provides more comfort.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
Impacts per Minute (IPM)	0 - 2650 min ⁻¹
Impact Energy	9,4 J
Adapted for SDS-MAX bits	✓
AWS ready	✓
Sound Power Level (L _{WA})	97 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	1,6 dB(A)
Tool weight with battery	6,3 - 7,7 kg
Product Dimensions (L x W x H):	496 x 113 x 258 mm
Vibration Level, Chiselling	6,5 m/s ²
Vibration Level, Chiselling with D-type Side Handle	6,5 m/s ²

User benefits

- Soft start for smooth start-ups
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery protection system automatically shuts off power when the battery level is low
- 12 bit angle settings allow the bit to be set at different positions for operating convenience

Link to product - www.makitauk.com



Related products

■ Optional AC

198993-4

Grease vessel for bit 100 ml



■ Other

User manual

Parts drawing