


AC5218



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2AO C IP67



Product characteristics	
Number of inputs and outputs	Number of analogue outputs: 2
Application	
Application	field installation
Electrical data	
Operating voltage [V]	18...31.6 DC
Max. current consumption from AS-i [mA]	50
Reverse polarity protection	yes
Additional voltage supply [V]	16...30 DC; (AUX)
Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 2
Outputs	
Number of analogue outputs	2; (connection of 2-wire, 3-wire and 4-wire actuators)
Analogue current output [mA]	4...20
Max. voltage drop across load for nominal current [V]	10
Resolution of analogue output	12 bit
Accuracy / deviations	
Measuring error [% of the final value]	0,5

AC5218



AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2AO C IP67

Operating conditions		
Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-25...70
Max. relative air humidity	[%]	90; (non condensing)
Max. height above sea level	[m]	2000
Protection		IP 67
Pollution degree		2
Tests / approvals		
EMC	EN 50295	
	EN 61000-6-2	
	EN 61000-6-3	
MTTF	[years]	125
UL approval	power supply	Class 2
AS-i classification		
AS-i version		2.11; 3.0
Extended addressing mode		no
AS-i master profile		M3; M4
AS-i profile		S-7.3.5
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	3.5
AS-i certificate		124001
Mechanical data		
Weight	[g]	183
Housing		housing for DIN rail mounting
Materials		PA; piercing contacts: CuSn6 nickel-plated and tin-plated
Displays / operating elements		
Display	analogue signal	LED, yellow channels AO1...AO2
	operation	LED, green AS-i, AUX
	errors	LED, red
Electrical connection		
Module connection		Flat cables
Accessories		
Items supplied		lower part
Accessories (optional)		Protective cap: M12, E73004
Remarks		
Remarks		There is an electrical separation between AS-i and AUX and between AS-i and the analogue outputs. The actuator supply on pins 1 and 3 can be used to supply the actuators. 3-wire connection possible via external link.
Pack quantity		1 pcs.




AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2AO C IP67

Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Connector: M12; coding: A



1	analogue output
2	actuator supply + 24 V
3	analogue output AO +
4	actuator supply 0 V
5	analogue output AO -
	functional earth FE