



Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Guide Hardware**

Connector Hardware Accessory Type: **Guide Socket Module**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Hardware Accessory Function	Guide Hardware
Connector Hardware Accessory Type	Guide Socket Module

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)

Candidate List Declared Against: JUNE 2025 (250)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1410477-2
MULTI-GIG GD PIN KEY/ESD NI PL



TE Part # 1410354-7
MULTI-GIG GUIDEPIN, 9MM 2.60

Customers Also Bought



TE Part #CAT-472-Z12553
HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT




TE Part #1410189-3
MULTIGIG RT T2 7RW H-LFT,ET2



TE Part #1-1469491-2
MULTIGIG RT GUIDEPIN, 9MM 2.60



TE Part #1-1469492-3
MULTIGIG RT 9MM GUIDE/ESD 90
DEG




TE Part #4-1617758-3
FCB-205-0219L=M83536/2-019L



TE Part #1-2000713-0
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #5747250-6
09 MSFL PLUG RA 318 (SL,FM)



TE Part #3-6318490-6
.5FHR04H,220,S,GIG,08/Sn,HT,NSYes

Documents

Product Drawings

MULTIGIG RT 9MM GUIDE/ESD 90 D

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1410353-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1410353-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1410353-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English