


Technical data sheet

Article number:
596-00160

TAG20-65T1FL



Product Group	Self-laminating and flag labels, thermal transfer
Product Family	Helatag 934
Material	Type 934, Polypropylene, white (934)
Colour	White (WH)
Adhesive	Acrylic
Application Method	The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.
Bundle Ø max.	10.00 mm
Bundle Ø min.	2.00 mm
Chem. Material Properties	Resistant to water, alcohol, gasoline, cleaning solutions and hydraulic oils
Curing Temperature	from 0 °C
Height (H)	30.00 mm
Height (H2)	35.00 mm
Labels per Row	1 pcs.
Operating Temperature	-30 °C to +80 °C
Package Content	1.000 pcs.
Package Content packed in	box
Print Method	thermal transfer print
Recommended Ribbon Type	TT822OUT
Storage conditions	50% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness.
Storage Temperature	+21 °C
Thermal Transfer Printer	TT431, TT4030
Thickness of Foil	19 µm
Width of Liner (WL)	69.00 mm
Width (W)	20.00 mm

