



TE Internal #: 5-1813099-1  
4 Position Housing, Housing for Female Terminals, Wire-to-Wire, 7 mm [.276 in] Centerline, Sealable, Black, Cable Mount (Free-Hanging)  
[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > Circular DIN Housings



Number of Positions: 4  
Connector & Housing Type: **Housing for Female Terminals**  
Mating Pin Diameter: 2.5 mm [.098 in]  
Connector System: **Wire-to-Wire**  
Centerline (Pitch): 7 mm [.276 in]

[All Circular DIN Housings \(59\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V

Body Features



Primary Product Color	Black
Connector & Keying Code	1

Contact Features

Contact Size	2.5mm
Contact Type	Socket
Mating Pin Diameter	2.5 mm[.098 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	7 mm[.276 in]

Dimensions

Row-to-Row Spacing	7 mm[.276 in]
Product Width	31 mm[1.22 in]
Product Length	32.9 mm[1.295 in]
Connector Height	32.9 mm[1.295 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Industry Standards

IP Rating	IP69K
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other



Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-R7602-T273  
ROUND CONNECTOR SYSTEM, PIN AND SOCKET



TE Part # 828922-1  
2,5MM CAVITY PLUG FOR 5,4MM DI




TE Part # 1-967402-1  
2,5MM ST-GEH KPL 4P




TE Part # 828920-1  
EINZELADERDICHUNG

Customers Also Bought







TE Part #5-929080-5  
2POS MQS REC COD E




TE Part #493576-1  
HSG 6P MICRO TIMER




TE Part #2050049-2  
3POS 2.8MM SENSOR PLUG ASSY




TE Part #2137352-3  
AMP-MCP 2.8mm TAB HOUSING,  
18POS




TE Part #2333679-1  
MINI-FUSE RETAINER




TE Part #2333679-2  
MINI-FUSE RETAINER




TE Part #2295764-1  
MINIRELAY HOLDER ASSEMBLY



TE Part #2312550-1  
FUSE+REL BOX ASSY GW H2 HARD  
WIRED BLOCK



TE Part #2304926-1  
MINI-RELAY RETAINER



TE Part #2295766-1  
MINIFUSE HOLDER ASSEMBLY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5-1813099-1\_A\_c-5-1813099-1-a.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-1813099-1\_A\_c-5-1813099-1-a.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-1813099-1\_A\_c-5-1813099-1-a.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English