

Non-sterile, accelerator-free nitrile cleanroom gloves, compatible with Class 100 (ISO 5) environments

- **Assured cleanliness:** Nitrilite™ 93-311 non-sterile gloves are specially designed for compatibility with Class 100 (ISO 5) cleanroom environments
- **Reduced allergy risks:** These cleanroom gloves are also free from latex proteins and chemical accelerators, reducing the susceptibility to Type I or Type IV allergic reactions
- **Heightened tactility:** Thanks to their optimally thick design, these silicone-free gloves ensure high levels of tactile sensitivity, making them ideal for precision handling



KEY FEATURES & BENEFITS

- **Class 100 (ISO 5) cleanroom compatibility:** Assured cleanliness
- **Latex-free nitrile formulation:** Type I latex allergy risks eliminated
- **No chemical accelerators:** Lower susceptibility to Type IV allergies and sensitivities

Industries

- Biotechnology Manufacturing
- Medical Device Manufacturing
- Electronics manufacturing

Recommended For

- Clean room cleaning and preparing
- Blending, compounding solids and liquids
- Spill or leakage cleanup
- Transferring liquids and solids
- Loading centrifuges and chromatography columns
- Assembly of parts
- Weighing and dispensing of solid and liquid raw materials



TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
Color	White
Shape	Ambidextrous
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2015
Regulatory/Standard Compliance	Category III, EN ISO 21420:2020, EN ISO 374-1:2016+A1:2018, EN ISO 374-5:2016, FDA21 CFR 177-2600-US Food Contact Approved, ISO 14001, UKCA
Packaging	50 gloves per inner bag; 2 inner bags per master polybag; 10 master polybags per (1000 gloves) per liner bag More sustainable packaging: These non-sterile gloves are packed in recyclable plastic packaging* and delivered in recycled cardboard shipper cases. *Pouch, bag and liner are made from polyethylene (PE) based film. Always check your local recyclable status as these materials may not be considered suitable for recycling in your location.
Storage	Keep away from direct sunlight; store in a dry place and keep in the original packaging. Keep away from ozone sources. If products are properly stored, as indicated, they won't lose their performances or change characteristics significantly. If products could be affected by ageing or storage, the expiry date is mentioned on the packaging materials.
Country of Origin	Malaysia
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
External Glove Surface	Textured Fingers
Internal Glove Surface	Powder-Free, Chlorinated
Cleanroom Class	Class 100/ISO 5
Shelf Life	5 Years
Tested for use with Chemotherapy Drugs	Yes
Protein Level	N/A: contains no natural rubber latex
Vulcanization Chemical Accelerators	None

Nitrilite®

93-311

Non-sterile Disposable Nitrile Cleanroom Glove

Physical Properties					Testing Method
Sizes	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	EN ISO 21420 ASTM D3767
Typical Length (mm/in)	300 / 12				
Palm Width (mm/in)	90 / 3.5	99 / 3.9	105 / 4.1	115 / 4.5	
Freedom from Holes	2.5 AQL				EN 455-1/ASTM D3577
Typical Particle Count ≥0.5µm (counts / cm²)	< 2,400 particles / cm²				IEST-RP-CC005.4
Target Single Wall Palm Thickness (mm/mil)	0.11 / 4.3				EN ISO 21420/ASTM D3767
Target Single Wall Finger Thickness (mm/mil)	0.17 / 6.7				EN ISO 21420/ASTM D3767
Target Single Wall Cuff Thickness (mm/mil)	0.09 / 3.5				EN ISO 21420/ASTM D3767

IONIC CONTENT

Concentration in µg/cm²	Typical	Concentration in µg/cm²	Typical
Calcium	<0.500	Potassium	<0.050
Chloride	<0.285	Sodium	<0.038
Lithium	<0.0004	Sulphate	<0.080
Magnesium	<0.050	Zinc	<0.300
Nitrate	<0.165		

ORDERING INFORMATION

SIZE	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
REORDER NO.	93311070	93311080	93311090	93311100

PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

