



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2176314-4
MELF SMA_A 180R 0.1% 15PPM 0102 0.3W

TE Part #3-1415020-1
PT570N20

TE Part #3-2319848-1
END STACK DIP 10P G RECESS SEAL TUBE

TE Part #5146893-2
1FHR,84,30A/V,S,C,S08,09,10

TE Part #5-103911-3
60 SYSTEM 50 RCPT ASSY DRRA

TE Part #5-104076-2
60 SYS50 HDR DRST SHRD W/SL SN

TE Part #1-928836-2
MOD2 PIN WITH A-PIN L/P

TE Part #1-1437581-1
ASE22RL=AUTOSLIDE DP

TE Part #7-2176246-6
CRGS2512 5% 1M8

TE Part #4-2176391-7
RQ 1206 37K4 0.1% 10PPM 5K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_149009-3_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_149009-3_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_149009-3_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro-Strip Interconnection System

English

Product Specifications



Application Specification

English

Agency Approvals

UL Report

English