



The C60H-DC supplementary protectors are used in direct current circuits (Industrial control and automations, transport, renewable energy...). They combine the following functions of circuit protection against short-circuit and overload currents, control and isolation.

IEC / EN 60947-2

UL1077

GB 14048.2

(Supplementary
Protector TC 3)



Catalogue numbers

Operating voltage (Ue)	12...250 V DC	12...500 V DC		
Rated voltage (Un)	250 V DC	500 V DC		
Number of poles	1P	2P		
Curve	C	C		
Number of modules of 9 mm	2	4		
Diagrams	DB116582 	DB116588 	DB116588 	
	Supply from above or below, observing the polarity	Supply from above	Supply from below	
Standards	UL1077	IEC 60947-2 EN 60947-2 GB 14048.2	UL1077	IEC 60947-2 EN 60947-2 GB 14048.2
Breaking capacity	5 kA / 250 V DC	20 kA / 110 V DC 10 kA / 220 V DC 6 kA / 250 V DC	5 kA / 500 V DC	20 kA / 220 V DC 10 kA / 440 V DC 6 kA / 500 V DC
Rating (A)*	UL 1077, IEC 60947-2, EN 60947-2, GB 14048.2			
0.5	MGN61500		MGN61520	
1	MGN61501		MGN61521	
2	MGN61502		MGN61522	
3	MGN61503		MGN61523	
4	MGN61504		MGN61524	
5	MGN61505		MGN61525	
6	MGN61506		MGN61526	
10	MGN61508		MGN61528	
13	MGN61509		MGN61529	
15	MGN61510		MGN61530	
16	MGN61511		MGN61531	
20	MGN61512		MGN61532	
25	MGN61513		MGN61533	
30	MGN61514		MGN61534	
32	MGN61515		MGN61535	
40	MGN61517		MGN61537	
Rating (A)*	IEC 60947-2, EN 60947-2, GB 14048.2			
50	MGN61518		MGN61538	
63	MGN61519		MGN61539	

*At 25°C / 77°F see temperature derating module 92515.

Technical data

- Tripping curves: C curve - Overcurrent protection for any type of application.
- Positive break indication - the green strip indicates that all the poles are open and allows work to be carried out on the downstream circuit in complete safety.
- Suitable for isolation as defined in IEC / EN 60947-2.
- Increase in the service life of the product: thanks to fast closure independent of the speed of action on the handle.
- Current limitation in the event of a fault: fast opening of the contacts prevents the loads from being destroyed in the event of a short-circuit.

Electrical technical data

Rated service breaking capacity (Ics)	75 % of the ultimate breaking capacity (Icu)
Power loss	see module 92517
Magnetic tripping (li)	8.5 In ($\pm 20\%$) (compatible with curve C)
Impulse voltage (Uiimp)	6 kV
Rated insulation level (Ui)	500 V DC

Endurance (O-C)



Electrical	<ul style="list-style-type: none"> ■ 3,000 cycles (where L/R=2 ms) ■ 6,000 cycles where the circuit is resistive
Mechanical	20,000 cycles

Complementary technical data

Degree of pollution	3				
Category	A (no delay in accordance with IEC / EN 60947-2 standards)				
Weight	<table> <tr> <td>1P</td> <td>128 g / 4.51 oz</td> </tr> <tr> <td>2P</td> <td>256 g / 9.03 oz</td> </tr> </table>	1P	128 g / 4.51 oz	2P	256 g / 9.03 oz
1P	128 g / 4.51 oz				
2P	256 g / 9.03 oz				

Environment





Tropicalisation	Relative humidity: 95 % at 55°C / 131°F in accordance with IEC 60068-2 and GB 14048.2 standards				
Temperature	<table> <tr> <td>Operating</td> <td>-25°C to 70 °C / -13°F to 158°F</td> </tr> <tr> <td>Storage</td> <td>-40°C to 85°C / -40°F to 185°F</td> </tr> </table>	Operating	-25°C to 70 °C / -13°F to 158°F	Storage	-40°C to 85°C / -40°F to 185°F
Operating	-25°C to 70 °C / -13°F to 158°F				
Storage	-40°C to 85°C / -40°F to 185°F				



⚠ Failure to match polarity during connection may lead to a fire hazard and/or serious injury.

- The connection polarity must be observed (marked on the front panel).
- Use only with direct current.
- If two poles are used in series for the American network, use at least a 12 inch / 30 cm cable.

Dimensions



C60H-DC

Kit for ring terminals


C60 accessories

Connection

DB118758	Rating	Tightening torque	Without accessory			With connection accessories		
			Copper cables UL 486A file no. #E216919	rigids	flexibles	with end piece	Terminal Al / Cu	Ring tongue terminal screw connection
			DB118758	DB118754	DB118753	DB118755	DB118756	DB118757
	≤ 25 A	2.5 N.m / 22 lb.in	2.5 to 25 mm ² #14 - #4 AWG	2.5 to 16 mm ² #14 - #6 AWG	50 mm ² / 1 AWG	Ø 5 mm	3 x 16 mm ² 3 x 6 AWG	3 x 10 mm ² 3 x 8 AWG
	> 25 A	3.5 N.m / 31 lb.in	2.5 to 35 mm ² #14 - #2 AWG	2.5 to 25 mm ² #14 - #4 AWG	-			
1	Insulated connector (see module 91906)							
2	Comb busbar (see module 91906)							
3	Terminal 50 mm ² Al / Cu	27060						
4	Ring tongue terminal screw connection	27053						
5	Ring tongue terminal connections kit Ø 5 mm, (upstream/downstream)	17400						
6	Insulated distribution terminal 4 pieces	19091						
		3 pieces	19096					

Assembly

7	Sealable terminal shield	26976
8	Inter-pole barrier	27001
9	Rotary handle	
	Switching sub-assembly	27046
	Disconnectable handle	27047
	Fixed handle	27048
10	Screw shield	26981
11	Padlocking accessory (to be locked in the "open" position)	26970
12	Spacer	27062
13	Dividable mounting plate	26996
14	Marker strip (see module 91900)	




C60 auxiliaries (see modules 90081 - 91103)

Indication

- 15** SD fault indicating switch
- 16** OF open/closed contact




Tripping

- 17** MN undervoltage release
- 18** MX + OF shunt release














- The electrical auxiliaries must be installed to the left of the circuit breaker and within a width of 54 mm.
- If the auxiliary SD contacts are associated with the tripping auxiliaries (MN, MX, etc.), they must be installed to the left of these auxiliaries.

Poles connected in series

Network selection			
Type	Earthing	Earthing central point	Isolated from earth
Source	Earthing polarity (in this case negative)	Earthing central point	Isolated polarities
Protected polarities	1 (1P isolation)	2	2
Diagrams (and type of faults)			

Selection of supplementary protector and pole connection

24 V ≤ Un ≤ 250 V	Single-pole	Two-pole	Two-pole
Upstream connection	Only if L+ polarity is earthed		
Downstream connection			
250 V < Un ≤ 500 V	Two-pole	Two-pole	Two-pole
Upstream connection			
Downstream connection			


Fault analysis (low earth connection resistance)

Fault A	<ul style="list-style-type: none"> ■ Isc maximum at U ■ only protected polarity concerned ■ all the poles of the protected polarity must have a breaking capacity \geq Isc max. at U 	<ul style="list-style-type: none"> ■ Isc maximum at $U/2$ ■ only positive polarity concerned ■ all the positive polarity poles must have a breaking capacity \geq Isc max. at $U/2$ 	<ul style="list-style-type: none"> ■ not relevant ■ the fault must be indicated by a permanent insulation monitor (PIM) and cleared (IEC/EN 60364)
Fault B	<ul style="list-style-type: none"> ■ Isc maximum at U ■ if one polarity (in this case positive) is protected: all the poles of this polarity must have a breaking capacity \geq Isc max. at U ■ if two polarities are protected, to ensure isolation: all the protections of the two polarities must have a breaking capacity \geq Isc max. at U 	<ul style="list-style-type: none"> ■ Isc maximum at U ■ the 2 polarities are concerned ■ all the poles of the two polarities must have a breaking capacity \geq Isc max. at U 	<ul style="list-style-type: none"> ■ Isc maximum at U ■ the 2 polarities are concerned ■ all the poles of the two polarities must have a breaking capacity \geq Isc max. at U
Fault C		<ul style="list-style-type: none"> ■ as for fault A ■ all the negative polarity poles must have a breaking capacity \geq Isc max. at $U/2$ 	<ul style="list-style-type: none"> ■ as for fault A with the same requirements

Tripping curves

C curve as in standard IEC 60947.2

- The operating range of the magnetic release is as follows between 7 I_n and 10 I_n .
- The curves show the cold thermal tripping limits when poles are charged and the electromagnetic tripping limits with 2 charged poles.
- The curves are used without any derating.



Temperature derating (according to UL 1077/ CSA22.2/ UL489A/ UL489/ IEC 60947-2 standards)

The maximum permissible current in a device depends on the ambient temperature in which it is placed. Ambient temperature is the temperature inside the enclosure or switchboard in which the devices have been installed.

The reference temperature is in the coloured column.

When several simultaneously operating devices are mounted side by side in a small enclosure, the temperature rise inside the enclosure causes a reduction in the current rating. A reduction coefficient of the order of 0.8 must therefore be allocated to the rating (already derated if it depends on the ambient temperature).

Temperature (°C)	-30	-25	-20	-15	-10	-5	0	5	10	15	20	25	30	35	40	45	50	55	60	65	70
Rating (A)	0.63	0.62	0.61	0.60	0.59	0.58	0.56	0.55	0.54	0.53	0.51	0.5	0.49	0.47	0.46	0.44	0.43	0.41	0.39	0.38	0.36
0.5	1.18	1.17	1.15	1.14	1.12	1.10	1.09	1.07	1.05	1.04	1.02	1	0.98	0.96	0.94	0.92	0.90	0.88	0.86	0.84	0.82
1	1.45	1.43	1.41	1.39	1.37	1.34	1.32	1.30	1.27	1.25	1.22	1.2	1.17	1.15	1.12	1.09	1.07	1.04	1.01	0.98	0.95
1.2	1.86	1.83	1.80	1.77	1.74	1.71	1.67	1.64	1.61	1.57	1.54	1.5	1.46	1.42	1.39	1.34	1.30	1.26	1.22	1.17	1.12
1.5	2.54	2.50	2.45	2.41	2.36	2.31	2.26	2.21	2.16	2.11	2.06	2	1.94	1.88	1.82	1.76	1.70	1.63	1.56	1.48	1.41
2	3.78	3.71	3.65	3.58	3.51	3.45	3.38	3.30	3.23	3.16	3.08	3	2.92	2.84	2.75	2.66	2.57	2.48	2.38	2.27	2.17
3	5.08	4.99	4.90	4.81	4.71	4.62	4.52	4.42	4.32	4.22	4.11	4	3.89	3.77	3.65	3.53	3.40	3.27	3.13	2.98	2.83
4	6.00	5.92	5.83	5.74	5.66	5.57	5.48	5.39	5.29	5.20	5.10	5	4.90	4.80	4.69	4.58	4.47	4.36	4.24	4.12	4.00
5	7.26	7.15	7.04	6.94	6.83	6.71	6.60	6.48	6.37	6.25	6.12	6	5.87	5.74	5.61	5.47	5.33	5.19	5.04	4.89	4.73
6	8.76	8.62	8.47	8.32	8.17	8.01	7.85	7.69	7.52	7.35	7.18	7	6.82	6.63	6.44	6.24	6.03	5.82	5.60	5.37	5.13
7	9.64	9.50	9.36	9.22	9.08	8.93	8.78	8.63	8.48	8.32	8.16	8	7.83	7.67	7.49	7.31	7.13	6.95	6.76	6.56	6.36
8	12.59	12.38	12.16	11.94	11.71	11.49	11.25	11.01	10.77	10.52	10.26	10	9.73	9.45	9.17	8.87	8.57	8.25	7.92	7.58	7.22
10	15.49	15.28	15.07	14.85	14.63	14.41	14.19	13.96	13.72	13.49	13.25	13	12.75	12.49	12.23	11.97	11.69	11.41	11.13	10.83	10.53
13	18.61	18.31	18.01	17.70	17.38	17.06	16.74	16.40	16.07	15.72	15.36	15	14.63	14.25	13.85	13.45	13.03	12.60	12.16	11.69	11.21
15	19.43	19.14	18.85	18.55	18.25	17.95	17.64	17.32	17.00	16.68	16.34	16	15.65	15.29	14.93	14.56	14.17	13.78	13.37	12.95	12.52
20	24.06	23.72	23.37	23.02	22.67	22.31	21.94	21.56	21.18	20.80	20.40	20	19.59	19.17	18.74	18.30	17.85	17.39	16.92	16.43	15.93
25	30.35	29.91	29.45	28.99	28.52	28.05	27.56	27.07	26.57	26.06	25.53	25	24.46	23.90	23.33	22.74	22.14	21.53	20.89	20.24	19.56
30	37.35	36.74	36.12	35.50	34.86	34.21	33.54	32.86	32.17	31.46	30.74	30	29.24	28.46	27.66	26.83	25.98	25.10	24.19	23.24	22.25
32	38.45	37.91	37.36	36.80	36.24	35.66	35.08	34.48	33.88	33.27	32.64	32	31.35	30.68	30.00	29.31	28.59	27.86	27.11	26.34	25.54
35	44.15	43.40	42.63	41.86	41.06	40.25	39.42	38.58	37.72	36.83	35.93	35	34.05	33.06	32.05	31.01	29.93	28.81	27.64	26.42	25.14
40	48.92	48.17	47.42	46.65	45.87	45.08	44.28	43.45	42.62	41.76	40.89	40	39.09	38.16	37.20	36.22	35.21	34.17	33.10	31.99	30.84
50	59.93	59.09	58.25	57.39	56.52	55.63	54.74	53.82	52.89	51.95	50.98	50	49.00	47.97	46.93	45.86	44.77	43.64	42.49	41.31	40.09
60	76.16	74.83	73.48	72.11	70.71	69.28	67.82	66.33	64.81	63.25	61.64	60	58.31	56.57	54.77	52.92	50.99	48.99	46.90	44.72	42.43
63	78.16	76.91	75.63	74.33	73.01	71.67	70.30	68.90	67.47	66.02	64.53	63	61.44	59.83	58.18	56.49	54.74	52.93	51.06	49.12	47.10