

servo motor SH3 055 0,71Nm,nokey,single,nobrake, 90°conn.IP54/IP65,9k RPM

SH30552P01A2000

EAN Code: 3606485295213

Main

Range compatibility	PacDrive 3
Device short name	SH3
Product or component type	Servo motor

Complementary

Maximum mechanical speed	9000 rpm	
[Us] rated supply voltage	115480 V	
Network number of phases	Three phase	
Continuous stall current	1.2 A	
Continuous stall torque	0.71 N.m at 115480 V three phase	
Continuous power	530 W	
Peak stall torque	2.5 N.m at 115480 V three phase	
Nominal output power	160 W at 115 V single phase 310 W at 230 V single phase 600 W at 400 V three phase 670 W at 480 V three phase	
Nominal torque	0.77 N.m at 115 V single phase 0.75 N.m at 230 V single phase 0.63 N.m at 400 V three phase 0.63 N.m at 480 V three phase	
Nominal speed	2000 rpm at 115 V single phase 4000 rpm at 230 V single phase 8000 rpm at 400 V three phase 8000 rpm at 480 V three phase	
Maximum current Irms	4.8 A	
Shaft end	Smooth shaft	
Shaft diameter	9 mm	
Shaft length	20 mm	
IP degree of protection	IP54 shaft bushing without shaft seal ring: conforming to IEC 60034-5 IP65 motor: conforming to IEC 60034-5 IP65 shaft bushing: conforming to IEC 60034-5	
Encoder type	Absolute single turn SinCos Hiperface	
Speed feedback resolution	128 periods	
Holding brake	Without	
Mounting support	International standard flange	
Motor flange size	55 mm	
Electrical connection	Rotatable right angled connector	

Torque constant	0.59 N.m/A at 120 °C	
Back emf constant	40 V/krpm at 20 °C	
Number of motor poles	3.0	
Rotor inertia	0.096 kg.cm²	
Stator resistance	17.4 Ohm	
Stator inductance	18.2 mH	
Maximum radial force Fr	370 N at 1000 rpm 290 N at 2000 rpm 260 N at 3000 rpm 230 N at 4000 rpm 220 N at 5000 rpm 200 N at 6000 rpm 190 N at 7000 rpm 190 N at 8000 rpm	
Maximum axial force Fa	40 N	
type of cooling	Natural convection	
Length	154.4 mm	
Centring collar diameter	40 mm	
centring collar depth	2 mm	
Number of mounting holes	4	
Mounting holes diameter	5.5 mm	
Circle diameter of the mounting holes	63 mm	
Product weight	1.5 kg	
Sizing reference	SH30552P	
Network number of phases	3	
Temperature copper hot	130 °C	
compatible drive output current 3s peak 2	6 A	
Electrical connection	rotatable right angled connector	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	19.000 cm
Package 1 Length	39.500 cm
Package 1 Weight	1.929 kg
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	6.424 kg
Unit Type of Package 3	P06
Number of Units in Package 3	12

Package 3 Height	75.000 cm	
Package 3 Width	80.000 cm	
Package 3 Length	60.000 cm	
Package 3 Weight	33.696 kg	

Logistical informations

Country of origin DE

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1429
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ead0850d-370a-47c5-8cf7-1d93c2c974a4
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins