



Part Number : [192130012](#)
Product Description : Avikrimp Wire Pin Terminal
for 16-14 AWG Wire, Mylar Tape Carrier
Series Number : 19213
Status : Active
Product Category : Crimp Terminals
Engineering Number : WP-8614T
Packaging Alternative : [192130011](#) (Bag)



Documents & Resources

Drawings

[192130012_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19213
Description	Avikrimp Wire Pin Terminal for 16-14 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 9.40mm
Product Name	Wire Pin,Avikrimp
UPC	800753053526

Agency

CSA	LR18689
UL	E32244

Physical

Flammability	94V-2
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.996/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	1.016µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	4.32mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880123</u>
Mini-Mac Applicator	<u>638850400</u>

This document was generated on Sep 24, 2025