




LED Spot PAR11 GU10 3.5W 200lm (35W) 827 38° Glass

Article number: 145045

BAI BaiSpot LED PAR11 MR11 GU10 3.5W 2700K 38° 200lm (35W) Glass Reflector 230V-240V 35x45mm LED-lamp

The so-called LED spots from the BaiSpot series are characterized by a much longer lifespan and significantly less energy consumption than their halogen predecessors. Due to the compact design, they are easily interchangeable. Spots are mainly used to provide directed light from the ceiling or wall. This glass version literally and figuratively has an extra beautiful appearance because the part through which the light shines is made entirely of glass. Ambient temperature range: -20°C to +40°C



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED Spot PAR11 GU10 3.5W 200lm (35W) 827 38° Glass
Brand	Bailey
Productseries	BaiSpot LED MV
Producttype	PAR11 Glass

ETIM specifications

Socket	GU10
Luminous flux [lm]	200 - 200
Nominal voltage [V]	220 - 240
Lamp power [W]	3.5 - 3.5
Colour temperature [K]	2700 - 2700
Diameter [mm]	35
Length [mm]	45
Dimmable	No
Lamp shape	Reflector
Beam angle [°]	38 - 38
Colour	White
Type of glass/cover	Prism
Lamp designation	Other
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	No
Luminous intensity [cd]	300
Rated luminous flux according to IEC 62612 [lm]	200
Power factor	0.4
Lamp efficacy [lm/W]	57
Nominal current [mA]	30 - 30
Colour of light according to EN 12464-1	Warm white < 3300 K
Housing colour	Other
Average nominal lifetime [h]	15000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	7500
Weighted energy consumption in 1000 hours [kWh]	4
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	Other
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming Touch and Dim	No

Dimming Zigbee	No
Dimming Bluetooth	No
Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	G
With twilight switch	No
Material of light bulb	Glass

Alternative articles



146177
LED Spot PAR11 GU10 DIM
3.5W (35W) 210lm 827 38°
Glass



80100041300
LED Ecobasic PAR11 GU10 DIM
3W (35W) 270lm 830 38°

Complementary articles



ZGU10250V
Ceramic Lampholder GU10 250V
100W