

ML Candle

ML CANDLE 827 E14 9W SLV

0035305

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035305
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Candle
Lamp finish	Frosted
Dimmable	No
Cap/Base	E14
Type	CANDLE
EAN code	5410288353050
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	450
Efficacy (Rated) (lm/w)	50
Watt (Nominal) (W)	9
Equivalent watt (W)	40
Voltage (V)	220-240

ML Candle

ML CANDLE 827 E14 9W SLV

0035305

DATA TABLE

General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035305
Energy saving lamp	Yes
Average life (Rated) (h)	10000
Energy class	A
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	Candle
Dimmable	No
Cap/Base	E14
Type	CANDLE
EAN code	5410288353050
E-number FI	4940410
E-number SE	8357573
Long description	
Product name	ML CANDLE 827 E14 9W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.5
Warm-up time to 60% of full light (max) (s)	<60
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	450
Lumen maintenance at end of nominal life (%)	60
Luminous flux (Nominal) (lm)	450

ML Candle

ML CANDLE 827 E14 9W SLV

0035305

Electrical data

kWh per 1000 hours burning time	9
Efficacy (Rated) (lm/w)	50
Watt (Rated) (W)	9
Watt (Nominal) (W)	9
Equivalent watt (W)	40
Voltage (V)	220-240
Lamp power factor	=0.55

Physical data


Weight (kg)	0.04
Lamp Length (mm) - C/L	125±2
Max. Lamp Diameter (mm) - D	39±1
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	14.00 x 5.00 x 5.00
Outer package dimensions (L x W x H) (cm)	26.00 x 11.00 x 16.00

ML Candle

ML CANDLE 827 E14 9W SLV

0035305

TECHNICAL DRAWINGS



ENERGY LABEL

