


Chip Monolithic Ceramic Capacitor

## Electrical Characteristics Data

### 0805 X7R 1500nF 50V (0805B154K500CP)

1. Dimension



Size Inch (mm)	L (mm)	W (mm)	T (mm)
0805 (2012)	2.00±0.15	1.25±0.10	1.25±0.10


2. Cap, DF, IR @25°C

(Cap, DF @1KHz, 1Vrms ; IR @50V, 120sec)

Item	Spec
Cap [nF]	1500 (±10%)
DF	≤ 2.5%
IR [G-ohm]	>0.67


3. Impedance/ESR-Frequency

(Equipment: 4294A)




4. Capacitance – Temperature Characteristics

(Equipment: 4284A)



5. Temperature Rise – Ripple Current


(Equipment: 11810)



6. Capacitance – DC Voltage Characteristics


(Equipment: 4284A; DC charge 60±5sec)

24V : -17.60% ; 50V : -54.23%



7. Capacitance – AC Voltage Characteristics

(Equipment: 4284A)



Last updated : 2017/10/18