



Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Covers



Protection & Strain Relief Accessory Type: **Pin Cover**

Primary Product Material: **Polycarbonate**

Product Profile: **Standard**

Connector Cover Type: **Terminating**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Pin Cover
Product Profile	Standard
Connector Cover Type	Terminating

Body Features

Primary Product Color	Clear
Primary Product Material	Polycarbonate

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 646502-1
2MM HM DUST PROTECTOR TYPE A /B

Also in the Series | Z-PACK 2mm HM




Backplane Coding Keys(60)

Backplane Connector Housings(4)

Backplane Guide Hardware(37)

Backplane Power Connectors(6)



 Board-to-Board Connector Contacts(2)	 Hard Metric Backplane Connectors (269)	 High Speed Backplane Connectors(1)	 Insertion & Extraction Tools(2)
 PCB Connector Covers(4)	 PCB Connector Shrouds(39)	 PCB Ferrules & Shields(19)	 Rectangular Power Connectors(87)

Documents

Product Drawings
2MM HM DUST PROTECTOR 6U CARD
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_646502-7_J.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_646502-7_J.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_646502-7_J.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Product Specification
English
Product Specification
English