

## Features

- Heavy Duty
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Brake
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

## RS PRO Castor Wheels

RS Stock No.: 0149207



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Black elastic solid rubber wheel 68 Shore A with aluminium centre. Hub on shielded ball bearings assembled with central spacer. Heavy duty castor. In zinc-chromium plated pressed steel, high thickness, turning on double rim of balls fitted in temperate thrust-bearings.









Assembled with self-locking nut. Dust cover ring on the balls.

## General Specifications

Rotation	Swivel
Weight Class	Heavy Duty
Load Capacity (Kg)	160
Load Capacity / 4pcs (Kg)	640
Tyre Material	Rubber
Hub Material	Aluminium
Bracket Material	Pressed Steel
Includes Brake	Yes
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

## Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 70°
---------------------------------	-------------

							
100x40	100x85	80x60	9x12	36	135	160	200

## Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	100
Wheel / Tread Width (mm)	40
Overall Height (mm)	135
Number of Fixing Holes	4
Fixing Hole Size (mm)	9x12
Hub Bearing Type	Ball Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	68
Levelling Extent (mm)	
Offset (mm)	36
Castor Weight (Kg)	1.640

## Fixing Centres Specifications

Fixing Centres (mm)	80x60
Fixing Centres Length (mm)	80
Fixing Centres Width (mm)	60

## Fixing Plate Specifications

Fixing Plate Dimensions (mm)	100x85
Fixing Plate Length (mm)	100
Fixing Plate Width (mm)	85