

Steel Rod Cutter XGT®, SC001G

40Vmax, 3 – 16 mm

Model SC001G is a Steel Rod Cutter powered by a 40VMax XGT Li-Ion battery

Cutting speed has been improved. With a 40VMax XGT battery and a Brushless motor, a D16 rebar can be cut in 1.7 seconds. Maximum cutting capacity ø16 mm



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Cutting time	1,7 s
Cutting Capacity Mild Steel (up to 400N/mm ²)	3 - 16 mm
Cutting Capacity Stainless Steel (up to 600N/mm ²)	3 - 16 mm
Sound Power Level (L _{WA})	89,6 dB(A)
Sound Pressure Level (L _{pA})	81,6 dB(A)
Product net weight	5,3 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	6,0 - 7,2 kg
Product Dimensions (L x W x H):	321 x 103 x 285 mm
Brushless Motor	✓

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing