

402.1683

INTERLOCKED SOCKET
16A 2P+E 6h 200-250V 60Hz 50Hz
130X260MM Screw terminals With
mechanical interlock



* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

EN IEC 60309-4 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	ADVANCE GRP Series
Synthetical description	INTERLOCKED SOCKET
Mounting version	FLUSH MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	16A
Poles	2P+E
Hour position	6h
Rated voltage	200-250V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	FLUSH MOUNTING
Colour	BLUE
Material	GRP Glass Reinforced Polyester
Protection degree	Watertight
Protection degree IP	IP66/IP67/IP69
Protection degree IK	IK11(-40°C)
Contact material	CuZn (brass)
Working temperature	-40°C/+60°C
GLOW WIRE	GW 960°C
Self-extinguishing UL94	V0
Padlock	ø5mm

■ DIMENSIONAL CHARACTERISTICS

Flange	130X260MM
--------	-----------

■ DOWNLOAD

Technical drawing [PDF]
 Technical drawing [STP]
 Technical drawing [DWG]
 Instruction manual

■ OPTIONS & VARIOUS NOTES

Options	With mechanical interlock
Notes	WITHOUT FUSE HOLDER
Catalogue notes	Supplied with stainless steel fixing screws.
	Empty base: ADVANCE-GRP System (fam. 579)