

VARTA Work Flex® Stadium Light rech.



Rechargeable water- and shock resistant LED Work Light with up to 1450 lumen (3 light modes), integrated hook and an adjustable stand für hanging or standing.



Information

- High performance LED
- Li-Ion rechargeable battery
- Integrated USB in, works with all Micro-USB cables
- Charging indicator
- Low battery indicator
- Shock proof 2m
- Splash-water and dust protected (IP54)
- Dirt-resistant surface
- Adjustable lighting area
- Adjustable stand (7 positions) for hanging or standing
- Integrated hook in handle
- VARTA brand quality ensured

Article Details

Ordernumber	18647 101 401
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 45.00 m
Runtime	(up to) 15 h
Total light output	(up to) 1450 lm
Equipped with	Li-Ion
Product Length / Depth mm	199.00
Product Width mm	42.00
Product Height mm	159.00
Product Weight g	438.00

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 996100	270.00	67.00	246.00	0.54
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 996117	300.00	282.00	273.00	2.58
PAL (Pallet)	128	40 08496 996124	800.00	1,200.00	1,242.00	103.39
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
4	8		32		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

