



SIMATIC, power supply module 120/230 V AC for ET200iSP, Ex db eb [ib] IIC T4 Gb, Ex db eb [ib] I Mb

Figure similar

General information	
Product brand name	SIMATIC
Product family	ET 200iSP
Product category	Power supply module
Product type designation	PS 120/230 V AC
Redundancy	
• Redundancy capability	Yes
Supply voltage	
Type of supply voltage	AC
Rated value (AC)	230 V; 120/230 V AC
permissible range, lower limit (AC)	85 V
permissible range, upper limit (AC)	264 V
Line frequency	
• permissible range, lower limit	47 Hz
• permissible range, upper limit	63 Hz
Mains buffering	
• bridging time for backplane bus, min.	20 ms
• buffering time for powerbus, min.	20 ms
• buffering time for IM 152 CPU, min.	20 ms
Input current	
Inrush current, max.	28 A
from supply voltage L1, max.	1.04 A; at rated voltage 230 VAC:0.45A at rated voltage 120 VAC:0.75A
At 50 Hz AC, max.	1.04 A
At 60 Hz AC, max.	1.04 A
Power loss	
Power loss, typ.	5 W; 5 W + 1.2 x total power loss of the electronics modules
Power loss, max.	21.3 W
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	No
Diagnoses	
• Diagnostic information readable	Yes; via IM 152
Diagnostics indication LED	
• Group error SF (red)	No
Ex(i) characteristics	
maximum values for connecting terminals for gas group IIC	
• Um (voltage at non-intrinsically safe connecting terminals), max.	264 V

Potential separation	
primary/secondary	Yes
between supply voltage and electronics	No
Degree and class of protection	
IP degree of protection	IP30
Standards, approvals, certificates	
CE mark	CE 0344
UKCA mark	DEKRA 21UKEX0033 Importer UK: Siemens plc Manchester M20 2UR
cULus	LISTED E334384
FM approval	CLASSIFIED 3025852
BIS	Yes
Suitable for safety functions	Yes
INMETRO certificate	UL-BR 12.0066
reference designation according to IEC 81346-2 (2009)	K
Use in hazardous areas	
<ul style="list-style-type: none"> • ATEX certificate • IECEx • CCC Ex • EAC Ex • FM marking • Explosion protection category for gas • Explosion protection category for dust • associated equipment (Ex ia) • associated equipment (Ex ib) 	KEMA 09 ATEX 0156 IECEx KEM 09.0070 2020322303002989 1Ex d e [ib] IIC T4 Gb PII Ex d e [ib Mb] I Mc Class I, Zone 1 AEx d e [ib] IIC T4 NI, Class I, DIV.2, GP. A,B,C,D T4 DIP, Class II, III, GP. E,F,G ATEX gas explosion protection, Zone 1 ATEX dust explosion protection, Zone 21 always install in corresponding enclosure No Yes
Marine approval	
<ul style="list-style-type: none"> • Germanischer Lloyd (GL) • American Bureau of Shipping (ABS) • Bureau Veritas (BV) • Det Norske Veritas (DNV) 	Yes Yes Yes Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> • min. • max. 	-20 °C 70 °C
Dimensions	
Width	60 mm
Height	190 mm
Depth	136.5 mm
Weights	
Weight, approx.	2 700 g

Classifications			
		Version	Classification
	eClass	14	27-24-26-11
	eClass	12	27-24-26-11
	eClass	9.1	27-24-26-11
	eClass	9	27-24-26-11
	eClass	8	27-24-26-11
	eClass	7.1	27-24-26-11
	eClass	6	27-24-26-11
	ETIM	10	EC002583
	ETIM	9	EC002583
	ETIM	8	EC002583
	ETIM	7	EC002583
	IDEA	4	3575
	UNSPSC	15	32-15-17-06

Approvals / Certificates

General Product Approval

For use in hazardous locations

[Miscellaneous](#)



For use in hazardous locations



[FM](#)



[Miscellaneous](#)



[CCC-Ex](#)

For use in hazardous locations

Maritime application



[Miscellaneous](#)



Environment



last modified:

6/7/2025