
Parker Product Datasheet



Quick coupling system with nominal diameter 5 for pneumatic, liquids and gas applications up to 35 bar. Available in brass, nickel-plated brass, or stainless steel.

PART NUMBER: 21KLKO06RVX
COUPLING HALF: Coupler
CONNECTION TYPE: Tube
CONNECTION SIZE: 4x6 MM
BODY MATERIAL: Stainless Steel 303
FUNCTION: Dry-Break (double shut-off)

PRODUCT OVERVIEW

Parker’s Series 21 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. Above average flow performance for liquid and gaseous media.

Markets:

- Industrial

- Electronics and energy management

- Rescue Equipment

- Life Science

- Machinery construction

- Material Handling

- Transportation

- Automotive

- Process

- Food & Beverage

Features/Benefits:

- Mini Industrial Coupling

- Single-hand operation for easy and fast connection

- European profile is the most representative profile worldwide

- Dry-break version available

- Additional safety locking system available to prevent unintentional disconnection

TECH SPECIFICATIONS

FOR FLUID TYPE	Water (Industrial, drinking, treated water)
BRAND	Parker
APPLICATION	Energy Management
PRODUCT STYLE	Quick-Connect
SLEEVE MATERIAL	Stainless Steel 303
TECHNOLOGY	Fluid & Gas Handling
VALVE TYPE	Standard Valve
CONNECTION TYPE	Tube with Hose Nut, without Spring Guard
OUTSIDE DIAMETER	16 mm
FUNCTION	Dry-Break (Double Shut-Off)
VALVE INCLUDED	Yes

QUANTITY PER BOX	2
DIVISION	Low Pressure Connectors Europe Division
TECHNOLOGY	Pneumatics
OPERATION TYPE	Sleeve
PRODUCT TYPE	Pneumatic Quick Couplings
SEAL MATERIAL	FKM
PLATING TYPE	Without Surface Treatment
APPLICATION	Trucks & Trailers
COUPLING HALF	Coupler
REGION OF ORIGIN	Germany
HEX SIZE	14 mm
BODY MATERIAL	Stainless Steel 303
APPLICATION	Industrial Machinery
MINIMUM OPERATING TEMPERATURE	5 °F
BRAND	Rectus
FLOW RATE	2.7 L/min (water)
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Electronics
INTERCHANGE TYPE	European Profile
MINIMUM OPERATING TEMPERATURE	-15 °C
CONNECTION SIZE	4x6 mm
INDUSTRY	General Industrial
SHAPE	Straight
INDUSTRY	Electronics
FOR FLUID TYPE	Chemicals (Paints, solvents, lubricants)
MAXIMUM OPERATING PRESSURE	8 bar

MAXIMUM OPERATING TEMPERATURE	392 °F
DIAMETER	5 mm (nominal)
COMPATIBLE FITTING	Series 21 Plug
INDUSTRY	Transportation
WEIGHT	0.033 kg
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
MAXIMUM OPERATING PRESSURE	507 psi
MAXIMUM OPERATING TEMPERATURE	200 °C
PRODUCT SERIES	Series 21