



## Main

|                             |                |
|-----------------------------|----------------|
| Range                       | New Unica      |
| Product or component type   | Socket-outlet  |
| Device presentation         | Mechanism      |
| Device mounting             | Flush          |
| Socket number               | 2              |
| Outlet poles configuration  | 2P + E         |
| Outlet standard             | CEE 7/3        |
| Outlet standard deviation   | Schuko         |
| Outlet standard description | Side earth     |
| Ground lug position         | 45° ground lug |
| Rated current               | 16 A           |

## Complementary






|                                |   |
|--------------------------------|---|
| Device application             | Power supply  |
| Cover type                     | With shutter  |
| [Ue] rated operational voltage | 250 V   |
| Network type                   | AC  |
| Network frequency              | 50/60 Hz  |
| Number of modules              | 4 modules   |
| Fixing mode                    | Clip-in   |
| Colour tint                    | Anthracite (RAL 7021)   |
| Connections - terminals        | IPT (Isolates Piercing Terminal)<br>Screw terminals   |
| Cable cross section            | 0...2.5 Mm² cable(s), 2 - cable stiffness: flexible<br>0...2.5 mm² cable(s), 2 - cable stiffness: rigid |
| Minimum load breaking capacity | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6  |
| Electrical durability          | 10000 cycles, cos phi = 0.8   |
| Insulation resistance          | > 5 MOhm at 500 V   |
| Dielectric strength            | 2000 V  |
| Material                       | PC: mechanism cover   |
| Surface finish                 | Painted   |
| Quantity per set               | Set of 1 flow-pack  |
| Standards                      | IEC 60884-1<br>UNE 20315-1-1<br>UNE 20315-1-2<br>DIN VDE 0620-1   |
| Product certifications         | AENOR[RETURN]EAC  |
| Embedding depth                | 31.1 mm   |
| Depth                          | 40.4 mm   |
| Width                          | 45 mm   |
| Height                         | 90 mm   |
| Net weight                     | 0.077 kg  |

|                               |   |
|-------------------------------|---|
| Surface treatment             | Painted   |
| Resistance to chemical agents | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -5...35 °C  |
| Ambient air temperature for storage   | -5...50 °C  |
| IK degree of protection               | IK04  |
| IP degree of protection               | IP21D   |
| Environmental characteristic          | Acetone<br>Bleach<br>UV resistant<br>Petrol<br>Oil<br>Alcohol<br>Window-cleaning fluid<br>Liquid soap |

## Offer Sustainability

|  |   |
|--|---|
| Sustainable offer status                       | Green Premium product   |
| REACH Regulation                               |  <a href="#">REACH Declaration</a>               |
| EU RoHS Directive                              | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free                         | Yes   |
| Mercury free                                   | Yes   |
| Sustainable packaging                          | Yes   |
| China RoHS Regulation                          |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information                     |  <a href="#">Yes</a>                           |
| Environmental Disclosure                       |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile                            | No need of specific recycling operations  |
| WEEE   | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins       |
| Minimum percentage of recycled plastic content | 53  |