

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, Plug straight M8, coding: A, on Socket straight M8, cable length: 1 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

Item number	1417494
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1BBA
Product key	AF1BBA
GTIN	4055626117102
Weight per piece (including packing)	34.3 g
Weight per piece (excluding packing)	33.3 g
Customs tariff number	85444290
Country of origin	DE

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M8
Number of positions	3
Coding type	A

Connection 2

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494


<https://www.phoenixcontact.com/gb/products/1417494>

Type	Socket straight M8
Number of positions	3

Cable/line

Cable length	1 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Cable weight	29 kg/km
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	3x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≥ 300 V
Test voltage	≤ 3000 V
Smallest bending radius, fixed installation	13 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable

1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing



Socket M8 x 1, straight

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable

1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Circuit diagram



Contact assignment of M8 plugs/sockets

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494
<https://www.phoenixcontact.com/gb/products/1417494>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1417494>

	UL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	60 V	4 A	-	-

	cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	60 V	4 A	-	-

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494

<https://www.phoenixcontact.com/gb/products/1417494>

Classifications

ECLASS

ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M 8MS/ 1,0-PVC/M 8FS - Sensor/actuator cable



1417494
<https://www.phoenixcontact.com/gb/products/1417494>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk