

UM7-TM (6X10) - Marker for terminal blocks



0830931

<https://www.phoenixcontact.com/gb/products/0830931>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, Strip, white, unlabeled, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 6 mm, Number of individual labels: 20, text field height: 10 mm, text field width: 6 mm



Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM7-TM ... UM labeling range includes terminal markers for Legrand terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

Commercial data

Item number	0830931
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BGE21C
Product key	BGE21C
Catalog page	Page 175 (C-3-2019)
GTIN	4046356910668
Weight per piece (including packing)	2.31 g
Weight per piece (excluding packing)	2.28 g
Customs tariff number	39269097
Country of origin	PL

UM7-TM (6X10) - Marker for terminal blocks



0830931

<https://www.phoenixcontact.com/gb/products/0830931>

Technical data

Product properties

Product type	Terminal marking
Area of application	Legrand
Pitch	6 mm
Type	high

Marking

Number of individual labels	20
Number of individual labels per row	10
Number of marker strips	2

Dimensions

Width	6 mm
Length	10 mm
Pitch	6 mm

Text field

Text field width	6 mm
Text field height	10 mm

Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Material	PC
Flammability rating according to UL 94	V2
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed

UM7-TM (6X10) - Marker for terminal blocks



0830931

<https://www.phoenixcontact.com/gb/products/0830931>

Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
---	-------------

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

UM7-TM (6X10) - Marker for terminal blocks



0830931

<https://www.phoenixcontact.com/gb/products/0830931>

Classifications

ECLASS

ECLASS-13.0

27281101

ETIM

ETIM 9.0

EC000761

UNSPSC

UNSPSC 21.0

39131500

UM7-TM (6X10) - Marker for terminal blocks



0830931

<https://www.phoenixcontact.com/gb/products/0830931>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk