

Rittal – The System.

Faster – better – everywhere.

► Fibre-optic splicing box with telescopic pull-out lockable – DK 7170.535

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Fibre-optic splicing box with telescopic pull-out lockable – DK 7170.535

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description: The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The rear section of the splicing box is completely open for cable entry, a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps, two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system.

Benefits: The telescopic pull-out provides optimum access to the splicing cassettes and cable clamp
The variable cassette fixture permits twist-proof installation of all standard splicing cassettes
The security lock fitted at the front protects against unauthorised access

Material: Sheet steel

Colour: RAL 7035

Supply includes: Splicing box
Cable routing clips
Security lock
Cassette lock
Cassette cover
Mounting accessories for patch panel

Note: Supplied without patch panels and splicing cassettes

Product description

Units: 1 U

Installation dimensions:	Installation depth: 363 mm
Number of splicing cassettes (max.):	2
Packs of:	1 pc(s).
Weight/pack:	5.88 kg
Copper weight (kg per piece):	0
EAN:	4028177166769
Customs tariff number:	94032080
ETIM 7.0:	EC001130
ETIM 6.0:	EC001130
eCl@ss 8.0/8.1:	19170113
eCl@ss 6.0/6.1:	19170107
Product description:	DK Fibre-optic splicing box, 1 U, For D: 363 mm, with telescopic pull-out, lockable
Approvals	
Certificates:	NA