

Parker Product Datasheet



The D1VW in NG06 (CETOP 03) is an on/off valve which provides high functional limits in combination with a very low, energy-saving pressure drop. It is optionally available with soft shift option or as explosion proof version according to ATEX and IECEx.

PART NUMBER: D1VW002CNJWS2
INPUT VOLTAGE: 24 VDC
SPOOL CODE: 002
SOLENOID OPTION: Soft shift
SPOOL POSITION: 3 positions, spring offset in position 0, operated in position a or b
MARKING: Standard
ORIFICE SIZE: 0.5 mm
SEAL MATERIAL: NBR

PRODUCT OVERVIEW

The directional control valve series D1VW in NG06 (CETOP 03 / NFPA D03) provides high functional limits up to 80 l/min in combination with a very low, energy-saving pressure drop due to optimized flow passages. The maximum pressure is 350 bar.

A wide variety of spools and options allows to design an unlimited number of hydraulic circuits. The D1VW is available with a soft shift option for smooth operation. An additional orifice in the solenoid anchor dampens the shifting time.

The D1VW*EE with explosion proof solenoids is based on the standard D1VW series. It is not only ATEX certified (explosion proof class is Ex e mb II T4 Gb for use in zone 1 and 2) but also equipped with IECEx compliant solenoids which are certified in accordance with IECEx standard

for equipment class 2 G. All explosion proof solenoids are DC design. The valves for AC operate with integrated rectifier.

Markets:

- Industrial

Features/Benefits:

- Compact, proven design that represents our long-term experience in hydraulics
- Wide range of spools - fits all hydraulic systems
- Shortest lead time - no warehousing necessary
- Optional soft shift option - for smooth operation
- Optional manual override
- Optional ex proof version

Applications:

- Suitable for general hydraulic applications

TECH SPECIFICATIONS

MAXIMUM OPERATING TEMPERATURE	60 °C
MINIMUM OPERATING TEMPERATURE	-25 °C
FOR FLUID TYPE	Hydraulic Oil According to DIN 51524
MAXIMUM FLOW RATE	60 L/min
SEAL MATERIAL	NBR
PORT CONNECTION	NG06 / CETOP 03
FUNCTION	3-Way
MOUNTING POSITION	Unrestricted
WEIGHT	2.1 kg
BODY MATERIAL	Cast Iron
MOUNTING TYPE	Subplate
PRODUCT SERIES	Directional Control Valve

MAXIMUM OPERATING PRESSURE	350 bar
DIVISION	Hydraulic Valve Systems Division Europe
CONNECTION TYPE	Connector as per EN 175301-803
OPERATION TYPE	Direct
MOUNTING POSITION	Preferably Horizontal
ACTUATION TYPE	Solenoid