

AI-XL 1,5- 8 BK - Ferrule



3201916

<https://www.phoenixcontact.com/gb/products/3201916>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 8 mm, sleeve length: 17.5 mm, color: black



Your advantages

- Previous methods of achieving correct conductor insulation are much more time consuming
- These ferrules can be used for short-circuit-proof cables

Commercial data

Item number	3201916
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH341S
Product key	BH341S
Catalog page	Page 485 (C-3-2019)
GTIN	4017918117368
Weight per piece (including packing)	0.238 g
Weight per piece (excluding packing)	0.238 g
Customs tariff number	85369010
Country of origin	DE

AI-XL 1,5- 8 BK - Ferrule

3201916

<https://www.phoenixcontact.com/gb/products/3201916>



Technical data

Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	Suitable for short-circuit-proof cables (NSGAFÖU) due to the significantly increased collar diameter
	UL certified
	Made from tin-plated electrolytic copper
	Design in accordance with UL 486F
	With "Easy Entry" (conical insertion area)
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG max.	16
Stripping length	13 mm

Dimensions

Dimensional drawing	
Sleeve length	17.5 mm
Length contact range	8 mm
Maximum stripping length	13 mm
Ferrule diameter	1.8 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.3 mm
Inner dimensions of the insulating collar	7 mm

Material specifications

Color	black (RAL 9005)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

AI-XL 1,5- 8 BK - Ferrule

3201916

<https://www.phoenixcontact.com/gb/products/3201916>



Mechanical properties

Technical data

Sleeve length	17.5 mm
---------------	---------

Environmental and real-life conditions

Ambient conditions


Optimum ambient temperature (storage/transport)	23.00 °C 50.00 % Storage in a dry and dark place in the original packaging is recommended
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

Standards and regulations

Design according to standard	UL 486F-E, NF C 63-023
------------------------------	------------------------

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI-XL 1,5- 8 BK - Ferrule

3201916

<https://www.phoenixcontact.com/gb/products/3201916>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3201916>



cULus Listed

Approval ID: E488001

AI-XL 1,5- 8 BK - Ferrule

3201916

<https://www.phoenixcontact.com/gb/products/3201916>



Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI-XL 1,5- 8 BK - Ferrule

3201916

<https://www.phoenixcontact.com/gb/products/3201916>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk