

EAGLE EDGE®

REF.
NEO060

RETRACTABLE TYPE FALL ARRESTER 6 M



**TESTED FOR
HORIZONTAL USE (EDGE)**

R ≥ 0.5

MAX


140 KG

**TESTED FOR USE
UP TO 140 KG**



COMPACT AND LIGHTWEIGHT

Without external shock absorber and with only 2kg weight, **EAGLE EDGE** is the most compact and complete on the market.



360° TOP SWIVEL

The swivel hook ensures an efficient anchorage and the correct position of the fall arrester.



SWIVEL + DROP INDICATOR

Fitted with a swivel connector with drop indicator, it follows all the moves of the user and ensure safety at a glance.



TECHNICAL SPECIFICATIONS

- **Vertical and horizontal use up to 140 kg**
- Total length 6 m
- 1 • Dyneema® webbing wide 25 mm (R>22kN)
- 2 • Composite housing PA Polyamid + fiber glass
- Without external shock absorber
- **Arrest force** < 600 daN
- **Static resistance** ≥ 15 kN
- 3 • Swivel anchor hook on top fitted with automatic twist lock connector in aluminum, opening 22 mm
- 4 • Automatic swivel connector on cable with fall indicator opening 28 mm in anodized aluminum
- **Weight** : 2 kg

DESCRIPTION

The **EAGLE EDGE** is a fall arrester equipped with a 6 m webbing line retracting automatically and fitted with 2 pawls braking immediately in case of fall and with an internal energy dissipating element. Lightweight and compact, it is recommended for both vertical and horizontal use for all users weighing up to 140 kg.

USE


Works on height with vertical fall hazards. Works in horizontal with fall hazard over a sharp edge ($R \geq 0,5$ mm).

NEW


OCTOBER 2024

New Dyneema® webbing colour


MINIMUM CLEARANCE AND FALL FACTORS



factor 1



horizontal use

REFERENCES	LENGTH AT REST (with connector)	EXTENDED LENGTH (with connector)	MINIMUM CLEARANCE		
			Maxi user weight	F1	Horizontale use
NEO060	532 mm	6000 mm	140 kg	≥ 2,60 m	≥ 4,00 m