


Timer Modules

Hermetically Sealed Relays



Electrical Control & Protection > Hermetically Sealed Relays > Timer > **Static Output**

Crouzet Hermetically Sealed Relays are ideal for switching electrical loads in harsh environments requiring extended lifetime. Available in multiple current options, voltage ratings and contact arrangements to meet the specific needs of each demanding applications in Aerospace, Railway, Nuclear and Defense.

Offer Description

- › Supply: Direct current
- › Contact arrangement: 1 SSO
- › Operating voltage: 24 VDC, 36 VDC, 48 VDC, 72 VDC and 110 VDC
- › Maximum current consumption: 30 mA at nominal voltage
- › Static output rating: 1 mA to 0.25A at nominal voltage
- › Time delay: Range N°1 from 0.25 to 63.75 secondes, Range N°2 from 0.25 to 63.75 minutes
- › Timing accuracy over temperature range: $\pm 10\%$
- › Repetitive fidelity: 2%
- › Recycling time: T1 = 100 ms $\pm$ 5 ms, T2 = 150 ms $\pm$ 5 ms
- › Min. control pulse time: 25 ms
- › Maximum supply voltage break time: D or E modes: 2 ms $\pm$ 0.2 ms
R mode: 0.3 ms $\pm$ 10%
- › Time delay programming: Time delay selection by wiring (see time delay & wiring chart)
- › Standard name & Time delay modes: THLAO: On operate (E mode)
THLOR: On release with positive control voltage (R mode)
THM or THLM: Monostable (D mode)
- › Dimensions of case: 44 mm max. (L) x 26 mm (W) x 25.7 mm (H) with coding keys M3
26 mm (L) x 26 mm (W) x 25.7 mm (H) for plug-in without fixing
- › Weight: 75 g max. with coding keys and 65 g max. for plug-in

Qualifications

- › Railway: NF CF 62 003 / IEC 60571 / IEC61000-4-4 / EN 50155 / IEC 61373 / EN 50121-3-2 / IEC 60068-2-11 / EN45545-2 / NF F 16-101/102



Standard Offer

	Coil voltage	Part Number	Connection		Mounting		Key	Qualification	P/N
			Type	Material	Flange	Screw			
Time Delay On Operate (THLAO)	24 VDC	RM10 EA1H 024D PG3K 00	Pin	Gold	Horizontal	M3	YUY	NF CF 62 003	MT3268042
	72 VDC	RM10 EA1H 072D PG3K 00	Pin	Gold	Horizontal	M3	YWY	NF CF 62 003	MT3268026
		RM10 EA1H 072D PG0X 00	Pin	Gold	Horizontal	-	-	326 000 MTE	MT3268140
	110 VDC	RM10 EA1H 110D PG3K 00	Pin	Gold	Horizontal	M3	YXY	NF CF 62 003	MT3268057
Time Delay On Release (THLOR)	24 VDC	RM10 RA1H 024D PG3K 00	Pin	Gold	Horizontal	M3	ZUY	NF CF 62 003	MT3268037
	72 VDC	RM10 RA1H 072D PG3K 00	Pin	Gold	Horizontal	M3	ZWY	NF CF 62 003	MT3268027
		RM10 RA1H 072D PG0X 00	Pin	Gold	Horizontal	-	-	326 000 MTR	MT3268150
	110 VDC	RM10 RA1H 110D PG3K 00	Pin	Gold	Horizontal	M3	ZYZ	NF CF 62 003	MT3268029
Monostable (THM)	24 VDC	RM10 DA1H 024D PG3K 00	Pin	Gold	Horizontal	M3	YUZ	NF CF 62 003	MT3268076
	36 VDC	RM10 DA1H 036D PG3K 00	Pin	Gold	Horizontal	M3	YYZ	NF CF 62 003	MT3268082
	72 VDC	RM10 DA1H 072D PG3K 00	Pin	Gold	Horizontal	M3	YWZ	NF CF 62 003	MT3268079
	110 VDC	RM10 DA1H 110D PG3K 00	Pin	Gold	Horizontal	M3	YXZ	NF CF 62 003	MT3268061

Accessories

Soldering sockets

For wires or PCB EN 45545

Non-Sealed sockets

With crimp contacts EN 45545

Sockets with FASTON lugs

With crimp contacts EN 45545

Coil Characteristics

Nominal operating voltage	24 VDC	36 VDC	72 VDC	110 VDC
Maximum operating	33 V	45 V	90 V	137 V
Minimum operating voltage	16.8 V	25 V	50 V	77 V
Hold voltage	14.5 V	21.2 V	42.5 V	66 V
Drop-out voltage	2.5 V	3.5 V	7 V	11 V
THLAO: On operate (E mode)	YUY	-	YWY	YXY
THLOR: On release with positive control voltage (R mode)	ZUY	-	ZWZ	ZXY
THM: Monostable (D mode)	YUZ	YYZ	YWZ	YXZ

Electrical Characteristics

Dielectric strength at sea level: All terminals to case	1500 Vrms / 50 Hz
Initial insulation resistance at 500 VDC:	> 1000 MΩ
Protection against overvoltage and reverse supply as per IEC 60571	Yes
Supply overvoltage	1.4 Un max / 1 s
Surge tests	± 1000 V / 50 μs
Transient bursts	± 2000 V / 50 ns

Electromagnetic Compatibility

Capacitive coupling, relay supply wires and temporisation wires as per IEC61000-4-4	2 KV
Direct coupling, supply and control wires as per IEC61000-4-4	2 KV
Max. length of wires	1 m

Environmental & Mechanical Characteristics

Operating temperature	-40 °C to +85 °C
Storage temperature	-55°C to +125 °C
Operating position	Any
Resistance against vibrations IEC 61373, Category I, Class B, Body mounted	Sinus: 20 g from 10 to 2 000 Hz Random: 0.3 g ² /Hz from 20 to 2000 Hz
Mechanical shock (any axis) IEC 61373, Category I, Class B, Body mounted	100 g - 6 ms
Shake resistance	40 g
Acceleration	15 g all directions
Leak rate	≤ 1x10 ⁻⁸ atm cm ³ /s
Damp heat	EC 60068-2-67, Test condition Cab
Salt mist	IEC 60068-2-11, 96 h
Fire & Smoke	NF F 16-101/102; EN45545-2
REACH & RoHS	Refer to REACH and RoHS associated certificates


Time Delay Programming

Timing range	Terminal to connect	Basic time	Timing range	Terminal to connect	Basic time
N°1 A1-B1 wired	B3-A2	0.25 s	N°2 A1-B1 not wired	B3-A2	0.25 min
	B3-A3	0.5 s		B3-A3	0.5 min
	B3-A4	1 s		B3-A4	1 min
	B3-B4	2 s		B3-B4	2 min
	B3-C4	4 s		B3-C4	4 min
	B3-C3	8 s		B3-C3	8 min
	B3-C2	16 s		B3-C2	16 min
	B3-B2	32 s		B3-B2	32 min
Time delay from 0.25 to 63.75 seconds			Time delay from 0.25 to 63.75 minutes		

Basic times are cumulative and time delay are obtained by addition of times affected to each wired terminals.


Connection Diagrams

Time Delay Modes





Recycling time = $T1 = 100\text{ ms} \pm 5\text{ ms}$, $T2 = 150\text{ ms} \pm 5\text{ ms}$
T = Temporisation

Electrical Diagram



Mountings



Coding keys for H mounting style

The coding example opposite is XXX

GUIDANCE CODES

U	V	W	X	Y	Z	
						Key 1
						Key 2
						Key 3

Key 2 **Key 1**

Key 3

View from connections side

Pin Pattern

A4	A3	A2	A1
B4	B3	B2	B1
C4	C3	C2	C1
D4	D3	D2	D1

Long part

Symbolic representation

A - A

5

0

-0.1

3.5

M3

© Crouzet - July 2026 - All rights reserved.

Registered office: 10 rue Docteur Henri Abel 26000 Valence (France) - RCS Romans 663 820 413 - Capital €29.110.000 - crouzet.com

Photos by Crouzet.

Registered trademark. Any reproduction, representation or distribution, even in part, is prohibited without prior written permission.

Warning: The technical information contained herein is for informational purposes only and does not constitute a contractual commitment or a guarantee of performance or fitness for any particular purpose. Crouzet and its subsidiaries reserve the right to make any changes without notice. It is essential to consult us regarding any specific use or application of our products, and it is the purchaser's responsibility to verify, in particular through appropriate testing, that the product is suitable for the intended use. Under no circumstances shall our warranty apply, nor shall we be held liable, for any use of our products – including, but not limited to, any modification, addition, or use in combination with other electrical or electronic components, circuits, mounting systems, or any other unsuitable equipment or substance – that has not been expressly approved by us prior to the conclusion of the sale. The applicable contractual terms and conditions are exclusively those set out in the Crouzet proposal accepted by the customer and in the current general terms and conditions of sale.