

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 5 mm . .. 13.2 mm, number of positions: 12, connection method: Crimp connection, series: RF, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

Commercial data

Item number	1615068
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABRAGW
Product key	ABRAGW
GTIN	4046356367882
Weight per piece (including packing)	109.14 g
Weight per piece (excluding packing)	105.09 g
Customs tariff number	85366990
Country of origin	DE

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Feedback, signal
	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
Housing material	Metal
Housing material	High-grade steel 1.4305
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

Electrical properties

Contact

Contact diameter	1 mm
Max. current	8 A
Nominal voltage U_N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connector

Type	straight
Direction of rotation	Counter direction

Connection 1

Head design	Socket
Head cable outlet	straight

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Head thread type	M23
------------------	-----

Cable/line

External cable diameter	5 mm ... 13.2 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

RF-12S2N8A8VDU - Cable connector




1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Drawings

Dimensional drawing



Dimensional drawing

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1615068>

	cUL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

	UL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-12S2N8A8VDU - Cable connector



1615068

<https://www.phoenixcontact.com/gb/products/1615068>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d07d2fe7-6b57-49ba-8132-dc236b0c48ac

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk