



ENGLISH

## Datasheet

# RS Pro Hydrocarbon Grease 50 ml Tube

RS Stock No: 556-446

**RoHS-2 Compliant  
(2011/65/EU):**



Typical Properties Colour	Light Brown
Temperature Range (°C)	-10 to +150
Evaporation Weight Loss (% 7 days @ 125°C)	3
Drop Point (IP32 / ISO 2176 (°C))	>250
Cone Penetration Un-worked (ASTM D 217 @ 20°C)	275
Base Oil	Mineral Oil
Thickener	Clay
UV Trace	No
Dielectric Strength (kV/mm)	30

Attribute	Value
Package Type	Tube
Grease Type	Hydrocarbon
Package Size	50 ml
Product Form	Grease
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+150°C
Colour	Beige