


543983 DGSL-16-10-PA Mini slide - Series: All

DGSL-16-10-PA/P1A/EA/Y11



543983 DGSL-16-10-PA Mini slide - Series: All

DGSL-16-10-PA/P1A/EA/Y11

Pos.	Part no.	Type	Note	Qty.	Unit
A	713748	DGSL-16-...- Set of wearing parts	Spare parts: 5, 6, 8, 11, 18, 21, 24, 27, 32, 33, 34, 35, 38, 43, 44	1	PC
1	200671	ISO 4762-M5X16-10.9 Socket head screw	Tightening torque 6 Nm / 4.4 lbf ft Use locking compound. See position 44	1	PC
2	696370	DGSL-16 Shaft screw	Tightening torque 6 Nm / 4.4 lbf ft	2	PC
3		DGSL-16 Yoke plate	Not available separately, see position 9 Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
4		DGST-20 Centring sleeve	Not available separately, see position 9 Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
5	208566	SB-22 Circlip		1	PC
6		WIFC1-8X11,5X3,2-NBR Wiper seal	Not available separately, see position 9+999 Grease using during assembly. See position 43	1	PC
7		DGSL-16 Bearing cap	Not available separately, see position 9 Grease using during assembly. See position 43	1	PC
8		B-17X1,5-N-FPM80 O-ring ISO3601	Not available separately, see position 9+999 Grease using during assembly. See position 43	1	PC
9	8197198	DGSL-16 Set of components		1	PC
10		DGSL-16-10 Guide module	Not available	1	PC
11	200049	ISO 4762-M5X35-10.9 Socket head screw		1	PC
12	686787	DGSL-16 Stop		1	PC
13	686803	DGSL-16 Covering		1	PC
14	204482	ISO 4762-M5X8-8.8 Socket head screw	Tightening torque 6 Nm / 4.4 lbf ft	1	PC
15	684374	DGSL-16 Moment compensator		1	PC
16		ISO 4762-M5X22-10.9 Socket head screw	Not available Tightening torque 6 Nm / 4.4 lbf ft	2	PC
17	699256	DGSL-16 Clamping component	Use locking compound. See position 44	2	PC
18	707129	DGSL-16 Buffer		2	PC
19		DYEF-S-M12-Y1 adjustment sleeve	Not available separately, see position 20	1	PC
20	1153004	DYEF-S-M12-Y1 Shock absorber	shock absorber -E	2	PC
21	707129	DGSL-16 Buffer		2	PC
22		DGSL-16-P adjustment sleeve	Not available separately, see position 23	1	PC
23	1179840	DYEF-M12-Y1 Shock absorber	shock absorber -P	2	PC
24	683974	DGSL-12/16/20-PFJ Buffer		2	PC

Pos.	Part no.	Type	Note	Qty.	Unit
25		DGSL-16-P1 adjustment sleeve	Not available separately, see position 26	1	PC
26	548375	DYEF-M12-Y1F Shock absorber	shock absorber -P1	2	PC
27	704893	DYSC/W-8- Buffer		1	PC
28		DYSW-7-10-Y1F Shock absorber	Not available separately, see position 29	1	PC
29	548072	DYSW-7-10-Y1F Shock absorber	Attention, please order position 30 as well shock absorber -Y11	2	PC
30	1165484	DAYH-7 reducing sleeve	Attention, please order position 29 as well shock absorber -Y11	2	PC
31	689900	IRA-08-S0060,8-B Piston rod	Glue with Loctite 401, adhesion surface area must free of oil and grease Warning! Disassembly requires recalibration.	1	PC
32		BA-K10D-020-A Complete piston	Not available separately, see position A Grease using during assembly. See position 43	1	PC
33	709441	DSNU-20 Nut	Tightening torque 2.7 Nm / 2.0 lbf ft Use locking compound. See position 44	1	PC
34		B-17X1,5-N-FPM80 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 43	1	PC
35		B-6,5X1-N-NBR70 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 43	1	PC
36		DGSL-16 Flow control plate	Not available separately, see position 41	2	PC
37		DGSL-16 Connection cap	Not available separately, see position 41	1	PC
38		OK-M5 Sealing ring	Not available separately, see position A	2	PC
39		B-M5 B Plug screw	Not available separately, see position 40 Tightening torque 2 Nm / 1.5 lbf ft	2	PC
40	712005	B-M5-B-OK Blanking plug		2	PC
41	714232	DGSL-16-...-ET Connection cover module		1	PC
42	200666	ISO 4762-M4X30-8.8 Socket head screw	Tightening torque 2.9 Nm / 2.1 lbf ft Use locking compound. See position 44	3	PC
43	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
44	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC