

Eaton 135569

Catalog Number: 135569

Eaton Moeller® series E58 Thru-beam photoelectric sensor, receiver, Sn=6m, 4L, 10-30VDC, light/dark, NPN, PNP, M18, insulated material 12100AQD07

General specifications



Product Name	Catalog Number
Eaton Moeller® series E58 Thru-beam photoelectric sensor	135569
	EAN
	4015081323623
Product Length/Depth	Product Height
152.4 mm	44.45 mm
Product Width	Product Weight
152.4 mm	0.23 kg

Certifications

UL Category Control No.: NRKH, NRKH7

CSA Class No.: 3211-07

CSA-C22.2 No. 14

CSA

UL 508

UL File No.: E117028

CE

CSA File No.: 50513

IEC/EN 60947-5-2

UL

Product specifications

Type

Optical sensors

Features

Straight beam

Device type

Receiver

Electric connection type

Plug-in connection

Enclosure material

Plastic

Enclosure type

Cylinder, screw-thread

Operating mode

Switching principle: Adjustable bright/dark switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Detector (for combination with source)

Short-circuit protection

Thru-light beam

Protection against polarity reversal

Voltage type

DC

Wire size

0

Connection type

4-wire

Plug-in connection M12 x 1

Cable sheath material

Polyurethane (PUR)

Light type

Polarity free red light

Degree of protection

NEMA 4

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004652.pdf

DA-DC-00004657.pdf

Drawings

eaton-proximity-switches-dimensions-003.eps

eaton-proximity-switches-dimensions-002.eps

eaton-proximity-switches-3d-drawing-002.eps

Installation instructions

IL05305002Z

mCAD model

DA-CD-90_28267_104

DA-CS-90_28267_104

IP67

Interface type

Other

LED indicator

Status indication of Switching state: Red LED

Switch function type

Programmable/configurable

Load current

Max. 100 mA (I_e, PNP)

Max. 250 mA (I_e, NPN, 120 > 50°C)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

100 g, Mechanical, Shock duration 3 ms

Optical surface material

Plastic

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at DC - max

30 V

Rated control supply voltage (U_s) at DC - min

10 V

Rated switching distance (S_n)

6000 mm

Reflector distance - min

0 mm

Sensor height

0 mm

Sensor length

56 mm

Switching distance - max

6000 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

142 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP

Sensor material

Insulated material

Wavelength of the sensor

0 nm

Width sensor

0 mm

Product category

Comet Series

Response time

7 ms

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-20 °C

Diameter sensor

18 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

0

Opening angle

0 °

Operational current (Ib) in the switched state at 24 V DC

30 A

Adjustment type

Manual adjustment



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia