



HT-SCE

TE Internal #: 397277-000

Ladder, High Temperature, 2:1, White, 1 Markers per Sleeve, 50 mm [2 in] Length, 4.76 mm [.187 in] Expanded Inside, HT-SCE, Printable Tubing

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > HT-SCE High Temperature Sleeves



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **High Temperature**

Shrink Ratio: **2:1**

Primary Product Color: **White**

Markers per Sleeve: **1**

[All HT-SCE High Temperature Sleeves \(51\)](#)

**Features**

**Product Type Features**

Printable Tubing Type	Ladder
Printable Tubing Grade	High Temperature

**Body Features**

Shrink Ratio	2:1
Primary Product Color	White
Markers per Sleeve	1

**Dimensions**

Product Length	50 mm[2 in]
Expanded Inside Diameter (Min)	4.76 mm[.187 in]
Recovered Inside Diameter (Max)	2.38 mm[.094 in]
Compatible Cable Diameter Range	2.4 – 3.84 mm[.094 – .151 in]

**Usage Conditions**

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

**Printer/Label Features**

Printer Technology	Thermal Transfer
--------------------	------------------



### Packaging Features

Packaging Quantity	1000
--------------------	------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 1-2186500-1 T3212-PRINTER</p>	 <p>TE Part # 1-2186502-1 T3224-PRINTER</p>	 <p>TE Part # 1-2186503-1 T3224-SWARE-PRINTER</p>	 <p>TE Part # 754073-000 TMS-RJS-RIBBON-4HT</p>
--	--	--	--



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

## Also in the Series | HT-SCE



Printable Tubing(16)

## Customers Also Bought



TE Part #34974  
TERMINAL,PIDG R 16-14HD 1/4



TE Part #640310-6  
UMNL SOK 12-10 AU/PHBZ



TE Part #277152-2  
TERMINAL,COPALUM R 2/0 3/8



TE Part #327717  
PIDG SPD 22-16 COMM 22-18MIL 4



TE Part #CAT-T3437-T548  
TMS-SCE Military Grade Sleeves



TE Part #325803  
TERMINAL,AMPOWER 300MCM 3/8



TE Part #754073-000  
TMS-RJS-RIBBON-4HT

## Documents

### Datasheets & Catalog Pages

[HT-SCE High Temperature Heat Shrink Identification System](#)

English

### Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English



---

**Instruction Sheets**

**Instruction Sheet (non U.S.)**

English