


VS-08-ST-H21-RJ45 - RJ45 male insert



1652729

<https://www.phoenixcontact.com/gb/products/1652729>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 male insert, CAT6, 8-pos., shielded, IDC displacement connection, for litz wire AWG 25 ... 24 and solid wires AWG 24, with strain relief

Your advantages

- Reliable 360° shield contact due to the proven crimp connection
- Easy installation with a crimping tool
- Pin insert for V.06 sleeve housing VS-08-T-H-RJ45/IP67

Commercial data

Item number	1652729
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	ABNAAG
Product key	ABNAAG
Catalog page	Page 350 (C-2-2019)
GTIN	4017918952853
Weight per piece (including packing)	5.4 g
Weight per piece (excluding packing)	3.957 g
Customs tariff number	85366990
Country of origin	TW

VS-08-ST-H21-RJ45 - RJ45 male insert



1652729

<https://www.phoenixcontact.com/gb/products/1652729>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Type	RJ45
Shielded	yes
Cable outlet	straight
Positions/contacts	8P8C

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	330 kV
Rated current	1 A
Contact resistance	< 20 mΩ (Contact) < 100 mΩ (shield)
Frequency range	to 250 MHz
Insulation resistance	> 500 MΩ (100 V DC)
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ (Wire – IDC)
Transmission medium	Copper
Transmission characteristics (category)	CAT6

Connection data

Connection technology

Connection method	Crimp connection
Connection cross section AWG	24 ... 25 (flexible) 24 (solid)
Conductor cross section	0.17 mm² ... 0.22 mm² (flexible) 0.2 mm² (solid)
Cable outlet, angle	180

Dimensions

VS-08-ST-H21-RJ45 - RJ45 male insert



1652729

<https://www.phoenixcontact.com/gb/products/1652729>

Width	11.7 mm
Height	14 mm
Length	30.2 mm

Material specifications

Color	red
Flammability rating according to UL 94	V2
Housing material	Steel, tin-plated
Contact material	Phosphor bronze
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	PC

Cable/line

External cable diameter	6.6 mm
Wire diameter including insulation	0.9 mm ... 1 mm
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C

Mounting

Mounting type	Crimp connection
---------------	------------------

VS-08-ST-H21-RJ45 - RJ45 male insert



1652729

<https://www.phoenixcontact.com/gb/products/1652729>

Classifications

ECLASS

ECLASS-13.0	27440114
-------------	----------

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-08-ST-H21-RJ45 - RJ45 male insert



1652729

<https://www.phoenixcontact.com/gb/products/1652729>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk