

Datasheet

RS PRO Tungsten Carbide Burrs

Stock No: 1947975,1947976,1947977



A

Shape A, Cylinder without end tothing

Diamond Cut: Universal cutting style.

Fast material removal.

Smooth finish.

Granular chip break.

Technical Information

- high-performance tungsten carbide
- with cross tothing





Application

To deburr, break edges, trim, process welding seams and surface processing

Fields of application

For high-alloy steels, non-rusting steels, acid-resistant steels, heat-resistant steels, die-casts and plastics

Technical Specifications:

RS No.	Burr Shape	Burr Pattern	 Burr Diameter	 Burr Length	 Shank Length	 Shank Diameter
1947975	Cylinder	Diamond	10	20	60	6
1947976	Cylinder	Diamond	12	25	65	6
1947977	Cylinder	Diamond	6	18	58	6