


Part Number: 192Fx25xWEC

Type	Size	Rating	Description
LED	M14	12Vdc	LED Indicator Flat Bezel with Leads

Dimensions in mm (Not to scale)



Part Number	Colour	Voltage	Typ. Current (mA)	Typ. Luminous Intensity (mcd)
192Fx251WEC	Green	12Vdc	14	280
192Fx252WEC	Yellow	12Vdc	15	190
192Fx253WEC	Red	12Vdc	22	220
192Fx257WEC	Blue	12Vdc	20	120
192Fx25WWEC	White	12Vdc	10	250

x = 0: Satin chrome bezel x = 1: Black chrome bezel x = 3: Grey chrome bezel

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Due to component tolerances, colour temperature variations may be observed
- 3 Storage/operating temperature range: -40 °C to +85°C
- 4 Sealed to IP67 above panel when the supplied gasket used
- 5 The plastic (polycarbonate) has limited chemical resistance
- 6 Marking: Part number, voltage rating and date code
- 7 Lead wires: 7/0.2 (24AWG) stranded copper, tinned annealed copper wire, PVC insulated
- 8 REACH SVHC compliant
- 9 This product contains free-machining brass and is RoHS compliant via exemption clause Annex iii 6 (c) of EU Directive 2011/65/EU [Copper alloy containing lead up to 4% by weight]