




 PRODUCT-DETAILS

MS116-6.3

MS116-6.3 Manual Motor Starter 4.0 ... 6.3 A



General Information

Extended Product Type	MS116-6.3
Product ID	1SAM250000R1009
EAN	4013614320323
Catalog Description	MS116-6.3 Manual Motor Starter 4.0 ... 6.3 A

Long Description	<p>The MS116-6.3 manual motor starter (also known as motor protection circuit breaker or manual motor protector) is a compact 45 mm width device with a rated operational current of $I_e = 6.3$ A. This device is used to manually switch on and off motors and to protect them reliably and without the need for a fuse from short-circuits, overload and phase failures. The manual motor starter offers a rated service short-circuit breaking capacity $I_{cs} = 50$ kA at 400 VAC and trip class 10A. Further features are the build-in disconnect function, temperature compensation, trip-free mechanism and a rotary handle with a clear switch position indication. The manual motor starter is suitable for three- and single-phase applications. Auxiliary contacts, signaling contacts, undervoltage releases, shunt trips, 3-phase bus bars, power in-feed blocks and locking devices for protection against unauthorized changes are available as accessory.</p>
------------------	---

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010

Popular Downloads

Data Sheet, Technical Information	2CDC131025D0201
Instructions and Manuals	2CDC131011M6802
Instructions and Manuals (Part 2)	2CDC131060M0202
Time-Current Characteristic Curve	1SAM200505F0009
I ² t Characteristic	1SAM200507F0001
	1SAM200507F0002
	1SAM200507F0003
Cut-off Current Characteristic	1SAM200508F0001
	1SAM200508F0002
	1SAM200508F0003
CAD Dimensional Drawing	2CDC001079B0201
Dimension Diagram	1SAM200422F0001

Dimensions

Product Net Width	45 mm
Product Net Height	90 mm
Product Net Depth / Length	85.6 mm
Product Net Weight	0.265 kg

Technical

Rated Service Short-Circuit Breaking Capacity (I _{cs})	(230 V AC) 50 kA
	(400 V AC) 50 kA
	(440 V AC) 6 kA
	(500 V AC) 6 kA
	(690 V AC) 2 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu})	(230 V AC) 75 kA
	(400 V AC) 75 kA
	(440 V AC) 18 kA
	(500 V AC) 15 kA
	(690 V AC) 3 kA
Rated Instantaneous Short-Circuit Current Setting (I _i)	78.8 A
Setting Range	4.0 ... 6.3 A
Rated Operational Power AC-3 (P _e)	(400 V) Three Phase 2.2 kW
Rated Operational Power AC-3e (P _e)	(400 V) Three Phase 2.2 kW
Rated Operational Voltage	Main Circuit 690 V AC
Rated Operational Current (I _e)	6.3 A
Rated Operational Current AC-3 (I _e)	6.3 A
Rated Operational Current AC-3e (I _e)	6.3 A
Rated Frequency (f)	Main Circuit 50 Hz
	Main Circuit 60 Hz
Rated Impulse	Main Circuit 6 kV

Withstand Voltage (U_{imp})	
Rated Insulation Voltage (U_i)	690 V
Power Loss	at Rated Operating Conditions per Pole 0.7 ... 1.8 W
Number of Poles	3P
Conventional Free-air Thermal Current (I_{th})	Main Circuit 6.3 A
Degree of Protection	Housing IP20 Main Circuit Terminals IP10
Pollution Degree	3
Electrical Durability	100000 cycle
Mechanical Durability	Nr. Operations 100000 cycle
Terminal Type	Screw Terminals
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Tightening Torque	Main Circuit 0.8 ... 1.2 N·m
Wire Stripping Length	Main Circuit 9 mm
Recommended Screw Driver	Pozidriv 2
Mounting Position	1 ... 6 any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Minimum Mounting Distance	Electrical Conductive Board, Horizontal - Up to 400 V 0 mm Electrical Conductive Board, Horizontal - Up to 690 V 1.5 mm Electrical Conductive Board, Vertical 75 mm Other Device Same Type, Horizontal 0 mm Other Device Same Type, Vertical 150 mm
Actuator Type	Rotary Handle
Contact Position Indication	ON / OFF
Standards	IEC/EN 60947-1 IEC/EN 60947-2 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1 IEC 60335-2-40 A2L

Technical UL/CSA

Short-Circuit Current Rating (SCCR)	Any UL Listed Fuses or Circuit-Breakers, Group Installations (480 V AC) 18 kA
	Any UL Listed Fuses or Circuit-Breakers, Group Installations (600 V AC) 5 kA
	Any UL Listed Fuses or Circuit-Breakers, Motor Disconnect (480 V AC) 18 kA
	Any UL Listed Fuses or Circuit-Breakers, Motor Disconnect (600 V AC) 5 kA
Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Horsepower Rating UL/CSA	(200 V AC) Three Phase 1 Hp (208 V AC) Three Phase 1 Hp (220 ... 240 V AC) Three Phase 1.5 Hp (440 ... 480 V AC) Three Phase 3 Hp (550 ... 600 V AC) Three Phase 5 Hp
Full Load Amps Motor Use	(200 V AC) Three Phase 6.3 A (208 V AC) Three Phase 6.3 A (220 ... 240 V AC) Three Phase 6.3 A (440 ... 480 V AC) Three Phase 4.8 A (550 ... 600 V AC) Three Phase 6.1 A

Locked Rotor Amps	(200 V AC) Three Phase 37.8 A (208 V AC) Three Phase 37.8 A (220 ... 240 V AC) Three Phase 37.8 A (440 ... 480 V AC) Three Phase 32 A (550 ... 600 V AC) Three Phase 36.8 A
General Use Rating UL/CSA	(600 V AC) 6.3 A
Connecting Capacity Main Circuit UL/CSA	Flexible 1/2x 16-12 AWG Stranded 1/2x 16-12 AWG
Tightening Torque UL/CSA	Main Circuit 10 in-lb

Environmental

Ambient Air Temperature	Around the Enclosure 0 ... +40 °C Operation -25 ... +70 °C Operation Compensated -25 ... +55 °C Storage -50 ... +80 °C
Ambient Air Temperature Compensation	Yes
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 25g
Resistance to Vibrations	2g 5 ... 150 Hz 5g 3 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA963005-4502
RoHS Declaration	1SAA963006-4501
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006539
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

ABB EcoSolutions	Yes
ABB Site Meeting Group Waste To Landfill Target	No non-hazardous waste is sent to a landfill
End Of Life Disassembling Instructions	1SAC200331H0001
Environmental Product Declaration - EPD	1SAC200359H0001 1SAC200384H0001

Certificates and Declarations

A2L Certificate – IEC	1SAA963000-4601
ABS Certificate	1SAA963000-0104
BV Certificate	1SAA963000-0204

CB Certificate	1SAA963005-2003 1SAA963006-2001
CCC Certificate	2024010307654705 2024010307656673
CQC Certificate	CQC2011010307506570 CQC2014010307744794
Cut-off Current Characteristic	1SAM200508F0001 1SAM200508F0002 1SAM200508F0003
Declaration of Conformity - CCC	2020980307003705 2020980307003043
Declaration of Conformity - CE	1SAD101100-3401
Declaration of Conformity - UKCA	1SAD201100-3401
DNV Certificate	1SAA963000-0304
DNV GL Certificate	1SAA963000-0304
EAC Certificate	1SAA963000-2701
GL Certificate	1SAA963000-0402
KC Certificate	1SAA963000-1501
LR Certificate	1SAA963000-0505
RMRS Certificate	1SAA918000-0704
UL Certificate	E137861-20001218

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	92 mm
Package Level 1 Depth / Length	95 mm
Package Level 1 Height	50 mm
Package Level 1 Gross Weight	0.28 kg
Package Level 1 EAN	4013614320323
Package Level 2 Units	carton 40 piece
Package Level 2 Width	280 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	11.586 kg
Package Level 2 EAN	4013614408694

External Classifications and Standards

Object Classification Code	F
ETIM 9	EC000074 - Motor protection circuit-breaker
ETIM 10	EC000074 - Motor protection circuit-breaker
eClass	V11.0 : 27370401
UNSPSC	39121521
IDEA Granular Category Code (IGCC)	4731 >> Manual Starters
E-Number (Finland)	3706009
E-Number (Norway)	4364275
E-Number (Sweden)	3111946

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
1SAM201901R1001	HKF1-11 Aux.-contact for front mounting	HKF1-11	1	piece
1SAM201901R1201	HKF1-11K Aux.-contact for frontmounting with Push-In terminals	HKF1-11K	1	piece
1SAM201901R1002	HKF1-20 Aux.-contact 2NO, front mounting	HKF1-20	1	piece
1SAM201901R1202	HKF1-20K Aux.-contact for frontmounting with Push-In terminals	HKF1-20K	1	piece
1SAM201901R1004	HKF1-01 Aux.-contact for front mounting	HKF1-01	1	piece
1SAM201901R1003	HKF1-10 Aux.-contact for front mounting	HKF1-10	1	piece
1SAM201902R1002	HK1-20 Aux.-contact 2 NO	HK1-20	1	piece
1SAM201902R1202	HK1-20K Aux.-contact 2 NO with Push-In terminals	HK1-20K	1	piece
1SAM201902R1001	HK1-11 Aux.-contact 1 NO + 1 NC	HK1-11	1	piece
1SAM201902R1201	HK1-11K Aux.-contact 1 NO + 1 NC with Push-In terminals	HK1-11K	1	piece
1SAM201902R1003	HK1-02 Aux.-contact 2 NC	HK1-02	1	piece
1SAM201902R1203	HK1-02K Aux.-contact 2 NC with Push-In terminals	HK1-02K	1	piece
1SAM201902R1004	HK1-20L Aux.-cont. w. 2 lead contacts 2 NO	HK1-20L	1	piece
1SAM201902R1204	HK1-20LK Aux.-cont. w. 2 leading contacts 2 NO, with Push-In terminals	HK1-20LK	1	piece
1SAM201903R1002	SK1-20 Signaling Contact 2 NO	SK1-20	1	piece
1SAM201903R1202	SK1-20K Signaling Contact 2 NO with Push-In terminals	SK1-20K	1	piece
1SAM201903R1005	SK1-20AR Signaling Contact, 2NO with screw terminals	SK1-20AR	1	piece
1SAM201903R1205	SK1-20ARK Signaling Contact, 2NO with Push-in Spring terminals	SK1-20ARK	1	piece
1SAM201903R1001	SK1-11 Signaling Contact 1 NO + 1 NC	SK1-11	1	piece
1SAM201903R1201	SK1-11K Signaling Contact 1 NO + 1 NC with Push-In terminals	SK1-11K	1	piece
1SAM201903R1004	SK1-11AR Signaling Contact, 1NO+1NC with screw terminals	SK1-11AR	1	piece
1SAM201903R1204	SK1-11ARK Signaling Contact, 1NO+1NC with Push-in Spring terminals	SK1-11ARK	1	piece
1SAM201903R1003	SK1-02 Signaling Contact 2 NC	SK1-02	1	piece
1SAM201903R1203	SK1-02K Signaling Contact 2 NC with Push-In terminals	SK1-02K	1	piece
1SAM201903R1006	SK1-02AR Signaling Contact, 2NC with screw terminals	SK1-02AR	1	piece
1SAM201903R1206	SK1-02ARK Signaling Contact, 2NC with Push-in Spring terminals	SK1-02ARK	1	piece
1SAM201910R1001	AA1-24 Shunt Trip 20-24V	AA1-24	1	piece
1SAM201910R1002	AA1-110 Shunt Trip 110V	AA1-110	1	piece
1SAM201910R1003	AA1-230 Shunt Trip 200-240V	AA1-230	1	piece
1SAM201910R1004	AA1-400 Shunt Trip 350-415V	AA1-400	1	piece
1SAM201904R1010	UA1-20 Undervoltage release 20V 50Hz / 24V 60 Hz	UA1-20	1	piece
1SAM201904R1001	UA1-24 Undervoltage release 24 V	UA1-24	1	piece
1SAM201904R1002	UA1-48 Undervoltage release 48V	UA1-48	1	piece
1SAM201904R1003	UA1-60 Undervoltage release 60V	UA1-60	1	piece
1SAM201904R1004	UA1-110 Undervoltage release 110V 110V 50Hz/120V 60Hz	UA1-110	1	piece
1SAM201904R1008	UA1-208 Undervoltage release 208V 60Hz	UA1-208	1	piece

1SAM201904R1005	UA1-230 Undervoltage release 230 V 50 Hz / 240 V 60 Hz	UA1-230	1	piece
1SAM201904R1006	UA1-400 Undervoltage release 400V	UA1-400	1	piece
1SAM201904R1007	UA1-415 Undervoltage release 415V 415V 50Hz/480V 60Hz	UA1-415	1	piece
1SAM201904R1009	UA1-575 Undervoltage release 575V 60Hz	UA1-575	1	piece
1SAM201906R1102	PS1-2-0-65 3-phase busbar for 2 MS116 / MS132, le=65A	PS1-2-0-65	1	piece
1SAM201906R1112	PS1-2-1-65 3-phase busbar for 2 MS116 / MS132 with 1 HK/SK, le=65A	PS1-2-1-65	1	piece
1SAM201906R1122	PS1-2-2-65 3-phase busbar for 2 MS116 / MS132 with 2 HK/SK, le=65A	PS1-2-2-65	1	piece
1SAM201916R1103	PS1-3-0-100 3-phase busbar for 3 MS116 / MS132, le=100A	PS1-3-0-100	1	piece
1SAM201906R1103	PS1-3-0-65 3-phase busbar for 3 MS116 / MS132, le=65A	PS1-3-0-65	1	piece
1SAM201916R1113	PS1-3-1-100 3-phase busbar for 3 MS116 /MS132 with 1 HK/SK, le=100A	PS1-3-1-100	1	piece
1SAM201906R1113	PS1-3-1-65 3-phase busbar for 3 MS116 / MS132 with 1 HK/SK, le=65A	PS1-3-1-65	1	piece
1SAM201916R1123	PS1-3-2-100 3-phase busbar for 3 MS116 /MS132 with 2 HK/SK, le=100A	PS1-3-2-100	1	piece
1SAM201906R1123	PS1-3-2-65 3-phase busbar for 3 MS116 / MS132 with 2 HK/SK, le=65A	PS1-3-2-65	1	piece
1SAM201916R1104	PS1-4-0-100 3-phase busbar for 4 MS116 / MS132, le=100A	PS1-4-0-100	1	piece
1SAM201906R1104	PS1-4-0-65 3-phase busbar for 4 MS116 / MS132, le=65A	PS1-4-0-65	1	piece
1SAM201916R1114	PS1-4-1-100 3-phase busbar for 4 MS116 /MS132 with 1 HK/SK, le=100A	PS1-4-1-100	1	piece
1SAM201906R1114	PS1-4-1-65 3-phase busbar for 4 MS116 / MS132 with 1 HK/SK, le=65A	PS1-4-1-65	1	piece
1SAM201906R1124	PS1-4-2-65 3-phase busbar for 4 MS116 / MS132 with 2 HK/SK, le=65A	PS1-4-2-65	1	piece
1SAM201916R1105	PS1-5-0-100 3-phase busbar for 5 MS116 / MS132, le=100A	PS1-5-0-100	1	piece
1SAM201906R1105	PS1-5-0-65 3-phase busbar for 5 MS116 / MS132, le=65A	PS1-5-0-65	1	piece
1SAM201916R1115	PS1-5-1-100 3-phase busbar for 5 MS116 /MS132 with 1 HK/SK, le=100A	PS1-5-1-100	1	piece
1SAM201906R1115	PS1-5-1-65 3-phase busbar for 5 MS116 / MS132 with 1 HK/SK, le=65A	PS1-5-1-65	1	piece
1SAM201906R1125	PS1-5-2-65 3-phase busbar for 5 MS116 / MS132 with 2 HK/SK, le=65A	PS1-5-2-65	1	piece
1SAM201907R1101	S1-M1-25 3-phase power infeed block Flat, for MS116 / MS132, 25mm ²	S1-M1-25	1	piece
1SAM201907R1102	S1-M2-25 3-phase power infeed block High, for MS116 / MS132, 25mm ²	S1-M2-25	1	piece
1SAM201907R1103	S1-M3-25 3-phase power infeed block Flat, for MS116 / MS132, 25mm ² , Type E	S1-M3-25	1	piece
1SAM201913R1103	S1-M3-35 3-phase power infeed block Flat, for MS116 / MS132, 35mm ² , Type E	S1-M3-35	1	piece
1SAM201914R1002	S1-PB1-25 1-phase power infeed block for MS116 / MS132 / MS132-T, 25mm ² , IEC	S1-PB1-25	1	piece
1SAM201914R1001	PB1-1-32 phase connecting link for MS116 / MS132 / MS132-T, le=32A	PB1-1-32	1	piece
1SAM201908R1001	BS1-3 Protection Cover for busbars empty places	BS1-3	1	piece
1SAM201909R1001	FS116 Screw fixing kit for MS116, MS/MO132 10 pieces packed	FS116	1	piece
GJF1101903R0001	SA 1 Locking Device	SA1	1	piece

GJF1101903R0002	SA 2 Padlock with 2 keys	SA2	1	piece
GJF1101903R0003	SA3 Locking Device, Set incl. padlock	SA3	1	piece
1SAM201911R1012	IB132-F Enclosure, GY/RD, IP65 3 times lockable	IB132-F	1	piece
1SAM201911R1010	IB132-G Enclosure, GY/BK, IP65 Standard version, 3 times lockable	IB132-G	1	piece
1SAM201911R1011	IB132-Y Enclosure, RD/YE, IP65 Emergency-STOP, 3 times lockable	IB132-Y	1	piece
1SAM201912R1010	DMS132-G Door Mounting Kit, GY/BK, IP65 Standard version, 3 times lockable	DMS132-G	1	piece
1SAM201912R1011	DMS132-Y Door Mounting Kit, RD/YE, IP65 Emergency-STOP, 3 times lockable	DMS132-Y	1	piece
1SAM201909R1021	MSAH1 Shaft Supporter suitable for MS116, MS132/MO132	MSAH1	1	piece
1SAM201920R1001	MSHD-LB Handle, IP64, black, 3 times lockable, defeatable, 0-I	MSHD-LB	1	piece
1SAM201920R1002	MSHD-LY Handle, IP64, red/yellow, 3 times lockable, defeatable, 0-I	MSHD-LY	1	piece
1SAM201920R1000	MSH-AR Shaft alignment ring suitable for MSHD and MSH handles	MSH-AR	1	piece
1SAM101923R0002	MSMN Driver w. screw for manual motor starters, 6x6	MSMN	1	piece
1SCA101655R1001	OXS6X130 SHAFT	OXS6X130	1	piece
1SAM101923R0012	MSMNO Driver w/o coding w. screw for manual motor starters, 6x6	MSMNO	1	piece
1SCA101659R1001	OXS6X180 SHAFT	OXS6X180	1	piece
1SCA101647R1001	OXS6X85 SHAFT	OXS6X85	1	piece
1SCA108043R1001	OXS6X105 SHAFT	OXS6X105	1	piece

Categories

Low Voltage Products and Systems → Circuit Breakers → Manual Motor Starters

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters

