

Agilia/Agilia IO

COMPACT GENTLE HEAT RADIATOR WITH POSSIBILITY OF REMOTE PILOTING



+ PRODUCT

COMFORT

- Homogeneous & gentle heat diffusion
- Double heating element: Aluminium + wide heating front film
- Integrated programming adjusting to the user's life rhythm
- Remote piloting through a smartphone or a tablet thanks to Cozytouch compatibility

SAVINGS

- Up to 45% of energy savings* thanks to integrated programming and absence/presence sensor**
- 6-command pilot wire: Comfort, Comfort -1°C, Comfort -2°C, Eco, Frost-free, Off
- Smart Pilot functions** memorising user's life rhythm & comfort requirements to drive optimal energy savings
- Open/closed window detection** function switching to Anti-frost mode as soon as a window opens
- Energy consumption indicator for responsible & informed use of the appliance
- ErP-compliant

USER-FRIENDLINESS

- Ergonomic LCD digital controls showing temperature and energy consumption
- 2 modes: Manual/Prog (Agilia)
- 3 modes: Manual/Prog/Auto (Agilia IO)
- ASP (Anti-Staining Process) to reduce staining on wall and equipment
- Easy installation: H-shaped vertical support

DESIGN

- Compact & elegant design to match all interiors
- Available in horizontal and vertical versions
- Colour: Textured matt white (RAL 9016)

GENTLE HEAT RADIATOR

500 TO 2000 W
(HORIZONTAL)

1500 TO 2000 W
(VERTICAL)



Model available***



Digital controls




Energy savings



Smart Pilot

Technology




Heating element type

Agilia/Agilia IO



- 1 Temperature and active mode display
- 2 modes: Manual/Prog (Agilia)
- 3 modes: Manual/Prog/Auto (Agilia IO)
- 2 Navigation buttons
- 3 Access to menu/validation
- 4 Energy consumption indicator

INSTALLATION DIMENSIONS



TECHNICAL DATA

OUTPUT (W)	DIMENSIONS (MM)							NET WEIGHT (Kg)
	WIDTH (W)	HEIGHT (H)	DEPTH (D)	A	B	B1	B2	
Agilia/Agilia IO Horizontal								
500	372	530	129	120.8	-	246	158.5	5.5
750	372	530	129	120.8	-	246	158.5	5.5
1000	446	530	129	194.8	-	246	158.5	6
1250	520	530	129	268.8	-	246	158.5	7.5
1500	594	530	138	342.8	-	246	158.5	9
2000	742	530	138	490.8	-	246	158.5	9
Agilia/Agilia IO Vertical								
1500	460	1392	145	280	1082	-	-	18
2000	460	1540	145	280	1230	-	-	19.5

*Available only for Agilia IO