

Metallized Polypropylene Film Capacitor (For Automotive)

NEW



Type **ECQUA [Class X2]**

In accordance with UL/CSA and European safety regulation class X2
Equipped with a safety mechanism


Features

- AEC-Q200 compliant
- High safety (safety function installed)
- High humidity resistance (THB test : 85 °C, 85 %, 240 V.AC, 1000 h)
- High Thermal shock resistance (-40 ⇔ 85°C, 1000 cycles)
- Flame-retardant plastic case and non-combustible resin
- RoHS compliant

Recommended applications

- Interference suppressors for automotive

Explanation of part number



Applicable standard

* It is certified as type ECQUA in the following approval.

| Approval | | Class | Certification |
|---------------|-------------------|----------|---------------|
| UL | UL60384-14 | Class X2 | UL |
| CSA | CAN/CSA E60384-14 | Class X2 | |
| Europe | EN60384-14 | Class X2 | VDE |
| International | IEC60384-14 | Class X2 | |

* When applying this capacitor to European and American safety standards, please use type designation and rating such as ECQUA, 0.1 μF.

* Approval number (File No.) of safety regulations are subject to revision without notice. Ask factory for a copy of the latest file No.

Specifications

| | |
|----------------------------|--|
| Category temperature range | -40 °C to +110 °C |
| Rated voltage | 275 V.AC |
| Rated capacitance | 0.10 μF to 4.7 μF |
| Capacitance tolerance | ±10 % (K), ±20 % (M) |
| Dissipation factor(tan δ) | C ≤ 1.0 μF : tan δ ≤ 0.1 % (20 °C, 1 kHz) C > 1.0 μF : tan δ ≤ 0.2 % (20 °C, 1 kHz) |
| Withstand voltage | Between terminals : 633 V.AC, 1183 V.DC, 60 s Between terminals to enclosure : 2050 V.AC, 60 s |
| Insulation resistance(IR) | C ≤ 0.33 μF : IR ≥ 15000 MΩ (20 °C, 100 V.DC, 60 s) C > 0.33 μF : IR ≥ 5000 MΩ · μF (20 °C, 100 V.DC, 60 s) C ≤ 0.47 μF : IR ≥ 2000 MΩ (20 °C, 500 V.DC, 60 s) |
| Maximum AC voltage * * | 310 V.AC |

* Use of this capacitor is limited to AC voltage (50 Hz or 60 Hz sine wave).

* A faint corona discharge may occur inside of the capacitor element at rated voltage, however there is no influence on the reliability of the capacitor.

* * Maximum AC voltage including line voltage fluctuation is 310 V.AC.

310 V.AC is not nominal continuous applied voltage, but only indicates maximum value including in the voltage of the power supply.

Basic nominal voltage is considered as 240 V.AC.

This maximum AC voltage is specified in only ECQUA type, not specified in other types.

Please refer to individual product specification, and contact us for further questions regarding design life.

Dimensions

Marking Example

| (A) side | (B) or (C) side |
|----------|-----------------|
| | |

Note : Only $\pm 10\%$ as cap. tol. be marked as "K".
 Note: Date code.

Unit : mm

Rating · Dimensions · Quantity

| Part No. | Capacitance e | Dimensions (mm) | | | | | | | Min. order Q'ty | |
|------------------------------------|------------------|-----------------|------|------|------|-----|-------|-----|-----------------|----------|
| | | L | T | H | F | Φd | P | Q | Straight | Cut lead |
| ECQUAAF104T () ECQUAAF104S () | 0.10 | 17.5 | 5.0 | 12.0 | 15.0 | 0.6 | 0±0.8 | 1.3 | 1000 | 1000 |
| ECQUAAF154T () ECQUAAF154S () | 0.15 | 17.5 | 6.0 | 13.0 | 15.0 | 0.6 | 0±0.8 | 1.3 | | |
| ECQUAAF224T () ECQUAAF224S () | 0.22 | 17.5 | 7.5 | 14.0 | 15.0 | 0.6 | 0±0.8 | 1.3 | | |
| ECQUAAF334T () ECQUAAF334S () | 0.33 | 17.5 | 9.0 | 16.0 | 15.0 | 0.6 | 0±0.8 | 1.3 | | |
| ECQUAAF474T () ECQUAAF474S () | 0.47 | 26.0 | 8.5 | 15.0 | 22.5 | 0.8 | 0±0.8 | 1.8 | | |
| ECQUAAF684T () ECQUAAF684S () | 0.68 | 26.0 | 10.0 | 17.0 | 22.5 | 0.8 | 0±0.8 | 1.8 | 500 | 500 |
| ECQUAAF105T () ECQUAAF105S () | 1.0 | 26.0 | 12.0 | 19.0 | 22.5 | 0.8 | 0±0.8 | 1.8 | 300 | 300 |
| ECQUAAF155T () ECQUAAF155S () | 1.5 | 31.0 | 12.0 | 22.0 | 27.5 | 0.8 | 0±0.8 | 1.8 | 200 | 200 |
| ECQUAAF225T () ECQUAAF225S () | 2.2 | 31.0 | 14.5 | 24.5 | 27.5 | 0.8 | 0±0.8 | 1.8 | | |
| ECQUAAF335T () ECQUAAF335S () | 3.3 | 31.0 | 19.0 | 29.0 | 27.5 | 0.8 | 0±0.8 | 1.8 | 150 | 150 |
| ECQUAAF475T () ECQUAAF475S () | 4.7 | 31.0 | 23.0 | 33.0 | 27.5 | 0.8 | 0±0.8 | 1.8 | 100 | 100 |

* () : Suffix for lead form