

LOW NOISE
62dB




LATEST GENERATION 2-POLE MOTORS



13A 230V



ANGLED PULL HANDLE PROTECTS MOTOR PUMP UNIT & AIR PRESSURE CONTROLS



LOW NOISE 2-CYLINDER MOTOR PUMP UNIT OPERATES AT JUST 62DB



TWIN ADJUSTABLE QUICK-RELEASE AIR CONNECTORS FOR QUICK AIR TOOL CHANGES



TANK PRESSURE & WORKING PRESSURE GAUGES WITH REGULATOR OPTIMISE AIR DELIVERY

IDEAL FOR WORK AREAS WITH RESTRICTED FLOOR SPACE



SMALLER OVERALL FOOTPRINT
390mm (W) x 400mm (D)

ITEM. 05483

SIP DD 2HP 50LTR LOW NOISE OIL-FREE VERTICAL DIRECT DRIVE COMPRESSOR

SPACE-SAVING VERTICAL DESIGN LOW NOISE AIR COMPRESSOR

PRODUCT OVERVIEW

The **SIP DD 2hp 50ltr Low Noise Oil-Free Vertical Direct Drive Compressor** is a versatile air compressor which features a space-saving vertical design, making it ideal for work areas with restricted floor space and limited storage capacity.

Built with a latest generation motor pump unit for improved airflow, this oil-free and low maintenance compressor delivers 9.6CFM piston displacement resulting in 4.7CFM Free Air Delivery (FAD). This makes it perfect for inflation tasks, nailing, stapling and airbrushing.

Operating at a low 62dB, it's also ideal for work areas where maintaining a low noise level is a consideration. This includes small-sized work areas, mobile applications and home workshops.

It's wheel-mounted design also supports easy movement in a variety of work area settings, whilst an angled pull handle helps to protect the motor pump unit and air pressure controls when stored or transported lay flat.

FEATURES & BENEFITS

✓ **LARGE TWIN-CYLINDER MOTOR PUMP UNIT WITH LATEST GENERATION 2-POLE MOTOR OPERATES AT A LOW 62DB, HELPING TO MAINTAIN A LOW NOISE WORK AREA. OIL-FREE FOR LOW MAINTENANCE USE**

Versatile air compressor is ideal for inflation tasks, nailing, stapling and airbrushing in small-sized work areas, mobile applications and home workshops. Vertical space-saving design offers a smaller overall footprint compared to traditional horizontal air compressors. This makes it ideal for work areas with restricted floor space.

Powerful 2hp motor pump unit operates at a low 62dB noise level and supports 9.6CFM piston displacement resulting in 4.7CFM Free Air Delivery (FAD) for air tools and inflation tasks.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 05483

SIP DD 2HP 50LTR LOW NOISE OIL-FREE VERTICAL DIRECT DRIVE COMPRESSOR

FEATURES & BENEFITS CONT.

This latest generation motor is designed to deliver a quieter performance compared to standard single cylinder SIP models. Larger motor fans improve cooling to maintain pump temperature and performance.

Oil-free for low maintenance use. This ensures no oil carry-through which delivers cleaner air to tools and equipment. The compressor will also transport more easily compared to oil-lubricated models, which have more potential to spill.

A braided delivery hose offers added durability when transferring compressed air to the receiver.

✔ 50LTR RECEIVER TANK SAFELY STORES COMPRESSED AIR READY FOR AIR TOOLS & INFLATION TASKS

Maintains a consistent air supply of up to 8bar max. pressure.

✔ TANK PRESSURE & WORKING PRESSURE GAUGES WITH REGULATOR OPTIMISE AIR DELIVERY

Provides an accurate display of current pressures for enhanced user operation.

✔ TWIN QUICK-RELEASE AIR CONNECTORS FOR FAST AIR TOOL CHANGES

The adjustable regulator (0-8bar) optimises air requirements to both quick-release connectors.

Also fitted with a quick-release air receiver condensate drain valve, which helps to reduce corrosion and maintain air quality to air tools.

✔ ANGLED PULL HANDLE FOR ADDED UNIT PROTECTION & SOLID WHEEL KIT WITH FRONT RUBBER FEET FOR OUTSTANDING MOBILITY AROUND THE WORK AREA

Allows full movement in a variety of work area settings for added flexibility.

Angled pull handle helps to protect the motor pump unit and air pressure controls when stored or transported lay flat.

WHAT'S IN THE BOX?

- 1x SIP DD 2hp 50ltr Low Noise Oil-Free Vertical Direct Drive Compressor
- 3mtr fitted mains cable with 230v/13A plug
- Wheel kit (2x solid wheels and front rubber feet), angled pull handle
- 2x air filters

APPLICATIONS & USES

IDEAL FOR SMALL WORK AREAS, MOBILE APPLICATIONS & HOME WORKSHOPS

PERFECT FOR INFLATION TASKS, NAILING, STAPLING & AIRBRUSHING

ITEM NO.	05483
INPUT SUPPLY	230v (13A)
MOTOR POWER	2hp (1.5kW)
RECEIVER SIZE	50ltr
PISTON DISPLACEMENT	9.6CFM (272ltr/min)
FREE AIR DELIVERY (FAD)	4.7CFM (131ltr/min)
MAX. AIR PRESSURE	116psi (8bar)
NOISE LEVEL	62dB
NET WEIGHT	30.5kg
GROSS WEIGHT	32.4kg
PRODUCT DIMENSIONS	840(H) x 390(W) x 400mm(D)
PACKAGED DIMENSIONS	880(H) x 380(W) x 380mm(D)