



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1

Electrical Characteristics

Insulation Resistance	1000 MΩ
Operating Voltage	300 VAC

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Type	Receptacle
Contact Retention Within Housing	Without
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Height	9.7 mm[.38 in]
Connector Length	20.94 mm[.67 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2-178488-4
UP 7.92 3P TAB HDR YELLO TYP 1



TE Part # 175151-5
AMP UNIVERSAL POWER CONN.REC C



TE Part # 178485-1
AMP U/P SGL ROW HDR HSG 5P V



TE Part # 2-178488-1
UP 7.92 3P TAB HDR NAT TYPE 1





TE Part # 175151-1
AMP UNIVERSAL POWER REC CONT.



TE Part # 175151-2
AMP UNIVE. POWER CONN REC CONT



TE Part # 4-178488-1
AMP U/P SGL ROW HDR ASSY V 4P



TE Part # 175152-3
UNIV POWER REC CONT



TE Part # 175152-4
UNIVESAL POWER REC CONT #20-16



TE Part # 3-178498-1
UP 7.92 3P TAB HDR NATL TYPE 1



TE Part # 175152-2
AMP UNIVE. POWER CONN REC CONT



TE Part # 175155-2
U/P REC CONT L/P



TE Part # 178479-1
AMP UP CAP HSG F/H 5P NATURAL



TE Part # 3-178488-1
UP 7.92 3P TAB HDR NAY TYPE 2



TE Part # 3-178488-4
UP 7.92 3P TAB HDR YELLO TYP 2



TE Part # 175155-1
UNIV POWER REC CONT L/P



TE Part # 175152-1
UNIVERSAL POWER REC



TE Part # 175151-4
UNIVESAL POWER REC CONT #26-22



TE Part # 175156-1
UNIV POWER REC CONT L/P



TE Part # 178488-1
UP 3.96 5P TAB HDR NAT TYPE 1


Also in the Series | AMP Universal Power



Connector Contacts(22)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(51)




Power Contacts(21)



Rectangular Connector Housings(112)



Rectangular Power Connectors(163)




Wire-to-Board Headers & Receptacles (51)


Customers Also Bought



TE Part #917683-1
2.5 SIGNAL DBL LOCK REC CONT L



TE Part #175152-2
AMP UNIVE. POWER CONN REC CONT



TE Part #170326-1
187 PL MKII REC. 18-14AWG PTBR



TE Part #770024-1
02P UMNLI IN-LINE CAP HSG KIT



TE Part #1939403-3
0.64 SMD 8P CAP ASSY V-TYPE




TE Part #179956-2
DYNAMIC D-5 REC CONT. M FORM




TE Part #1-170823-3
187 FASTON SLEEVE,REC., TRANSPARENT,NAT



TE Part #178483-1
UP 3.96 6P PLUG HSG NATRL



TE Part #173974-1
187 HSG. PL MKII REC. NAT



TE Part #321235
RECEPT, FASTON SPLICE 22-10

Documents

Product Drawings

UP 3.96 5P PLUG HSG NATRL

English

UP 3.96 5P PLUG HSG NATRL

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_178482-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_178482-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_178482-1_O.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_178482-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_178482-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_178482-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Crimping of Universal Power Contact](#)

English

[Product Specification](#)

Japanese

[AMP Universal Power Connector](#)

Japanese

Instruction Sheets

[AMP UNIVERSAL POWER CONNECTOR SERIES](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English