



WX-LED

A practical and robust double-sided sign suited to public walkways, enclosed car parks or educational establishments.

- Extended life, high performance LED light source
- Energy saving LED control technology
- Ingress rated to IP65
- Screw fixed diffuser
- 27m viewing distance



Specification	Self-contained Electrical & operational
Input voltage	220-240v 50Hz
Operation	Maintained
Duration	3 hours
Battery	High temperature nickel metal hydride
Charger	Constant current
Charging monitor	Green LED
Recharge period	24 hours
Lamp	LED strip light
Lamp rating:	1w
Consumption:	NM- 12mA, M-27mA
	Construction & installation
Cable entry	Rear and moulded locations, 20mm
Construction	Polycarbonate, high grade plastic in white
Environment	0 – 25 °C
Ingress class	IP65
Dimensions lwd (mm)	400 x 140 x 166 (base - 49, diffuser – 155)
Weight (kg)	2.1
Product standards	Designed & manufactured to meet BSEN60598.2.22 product regulations
To order	
Product code	Description
DV3LS1XE22	 Double sided sign M3, with euro pictogram arrow down on both sides
DV3LS1XE36	 Double sided sign M3, with euro pictogram arrow left one side right the other