

SKINDICHT® ME-M

SKINDICHT® ME-M, enlarger, enables the use of cable glands with larger connection threads than the existing threaded holes



Temperature-resistant



Reliability



Space requirement



Assembly time

Benefits

Enables the use of cable glands with larger connection threads than the existing threaded holes

Application range

Machines
Devices
Housings

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

On request:

with O-ring fitted

Last Update (12.11.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® ME-M

Material:	Nickel-plated brass
Temperature range:	-60°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® ME-M

Article number	Thread, male M1	Thread, female M2
SKINDICHT® ME-M		
52104450	12 x 1.5	16 x 1.5
52104452	16 x 1.5	20 x 1.5
52104454	20 x 1.5	25 x 1.5
52104456	25 x 1.5	32 x 1.5
52104458	32 x 1.5	40 x 1.5
52104460	40 x 1.5	50 x 1.5
52104462	50 x 1.5	63 x 1.5
SKINDICHT® ME-M hexagon		
52104463	63 x 1.5	75 x 1.5

Last Update (12.11.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16