

PRO Wood Circular Saw Blade

PRO



- ▶ For cutting all types of solid wood and wood-based panel materials used to make stairs, window frames, doors, and furniture
- ▶ Highly efficient for woodworkers and wood joiners: Long Life
- ▶ Lasts up to 1.3x times longer than a Bosch Eco for Wood Circular Saw Blade
- ▶ Bore works with or without reduction rings to fit different sizes



PRODUCT PROPERTIES								ORDERING INFORMATION				
Outer diameter mm	Bore size mm	Bore with reduction ring mm	Bore with reduction ring inch	Number of teeth	Width of cut (b1) mm / Base bl. thickness (b2) mm	Max. rotation speed (RPM)	Tooth shape	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
85	15	-	-	20	1.1/0.7	18,000	ATB	C1a	1	1	3165140754279	2 608 643 071
130	16	-	-	9	2/1.4	11,500	ATB/FT	C1a	1	1	3165140239851	2 608 640 774
130	16	-	-	18	2/1.4	11,500	ATB/FT	C1a	1	1	3165140239868	2 608 640 775
130	20	16	-	20	2.4/1.4	11,500	ATB	C1a	1	1	3165140193764	2 608 640 582
130	20	16	-	30	2.4/1.4	11,500	ATB	C1a	1	1	3165140193771	2 608 640 583
130	20	16	-	12	2.4/1.4	11,500	ATB	C1a	1	1	3165140373494	2 608 641 167
140	20	12.75	-	20	2.4/1.4	10,500	ATB	C1a	1	1	3165140193801	2 608 640 586
140	20	12.75	-	12	2.4/1.4	10,500	ATB	C1a	1	1	3165140373500	2 608 641 168
150	20	16	-	24	2.4/1.4	10,000	ATB	C1a	1	1	3165140193863	2 608 640 592
150	20	16	-	36	2.4/1.4	10,000	ATB	C1a	1	1	3165140193870	2 608 640 593
150	20	-	-	18	2/1.4	10,000	ATB/FT	C1a	1	1	3165140239929	2 608 640 781
150	20	16	-	12	2.4/1.4	10,000	ATB	C1a	1	1	3165140373517	2 608 641 169
160	16	-	-	12	2.2/1.6	9,500	ATB/FT	C1a	1	1	3165140239950	2 608 640 784
160	16	-	-	18	2.2/1.6	9,500	ATB/FT	C1a	1	1	3165140239967	2 608 640 785
160	20	16	-	24	2.6/1.6	9,500	ATB	C1a	1	1	3165140193900	2 608 640 596
160	20	16	-	36	2.6/1.6	9,500	ATB	C1a	1	1	3165140193917	2 608 640 597
160	20	16	-	48	2.6/1.6	9,500	ATB	C1a	1	1	3165140195072	2 608 640 732
160	20	-	-	12	2.2/1.6	9,500	ATB/FT	C1a	1	1	3165140239974	2 608 640 786
160	20	-	-	18	2.2/1.6	9,500	ATB/FT	C1a	1	1	3165140239981	2 608 640 787
160	20	16	-	12	1.8/1.2	9,500	ATB	C1a	1	1	3165140373524	2 608 641 170
160	20	16	-	24	1.8/1.2	9,500	ATB	C1a	1	1	3165140373531	2 608 641 171
160	20	16	-	48	1.8/1.2	9,500	ATB	C1a	1	1	3165140373548	2 608 641 172
160	20	16	-	12	2.6/1.6	9,500	ATB	C1a	1	1	3165140373555	2 608 641 173
165	20	16	-	12	1.7/1.2	9,000	ATB/FT	C1a	1	1	3165140660259	2 608 642 600
165	20	16	-	24	1.7/1.2	9,000	ATB/FT	C1a	1	1	3165140660266	2 608 642 601
165	20	16	-	36	1.7/1.2	9,000	ATB	C1a	1	1	3165140660273	2 608 642 602
165	30	-	-	24	2.6/1.6	9,500	ATB	C1a	1	1	3165140193962	2 608 640 602
165	30	-	-	36	2.6/1.6	9,500	ATB	C1a	1	1	3165140193979	2 608 640 603
165	30	-	-	18	2.2/1.6	9,000	ATB/FT	C1a	1	1	3165140240000	2 608 640 789
165	30	-	-	48	2.6/1.6	9,500	ATB	C1a	1	1	3165140373579	2 608 641 175
180	30	20	-	24	2.6/1.6	8,500	ATB	C1a	1	1	3165140194020	2 608 640 608
180	30	20	-	36	2.6/1.6	8,500	ATB	C1a	1	1	3165140194037	2 608 640 609
184	16	-	-	24	2.2/1.6	8,000	ATB/FT	C1a	1	1	3165140240062	2 608 640 795
184	16	-	-	24	2.6/1.6	8,000	ATB	C1a	1	1	3165140263429	2 608 640 817
184	16	-	-	36	2.6/1.6	8,000	ATB	C1a	1	1	3165140263436	2 608 640 818
184	16	-	-	48	2.6/1.6	8,000	ATB	C1a	1	1	3165140373630	2 608 641 181
184	30	-	-	24	2.6/1.6	8,000	ATB	C1a	1	1	3165140194044	2 608 640 610
184	30	-	-	36	2.6/1.6	8,000	ATB	C1a	1	1	3165140194051	2 608 640 611
190	20	16	-	24	2.6/1.6	8,000	ATB	C1a	1	1	3165140194068	2 608 640 612
190	20	16	-	36	2.6/1.6	8,000	ATB	C1a	1	1	3165140194075	2 608 640 613
190	20	16	-	48	2.6/1.6	8,000	ATB	C1a	1	1	3165140194082	2 608 640 614
190	20	16	-	24	2.4/1.6	8,000	ATB/FT	C1a	1	1	3165140240109	2 608 640 799
190	30	-	-	24	2.6/1.6	8,000	ATB	C1a	1	1	3165140194099	2 608 640 615
190	30	-	-	36	2.6/1.6	8,000	ATB	C1a	1	1	3165140194105	2 608 640 616
190	30	-	-	48	2.6/1.6	8,000	ATB	C1a	1	1	3165140194112	2 608 640 617
190	30	-	-	12	2.4/1.8	8,000	ATB/FT	C1a	1	1	3165140240116	2 608 640 800
190	30	-	-	24	2.4/1.8	8,000	ATB/FT	C1a	1	1	3165140240123	2 608 640 801
190	30	-	-	16	2/1.3	8,000	ATB	C1a	1	1	3165140373661	2 608 641 184
190	30	-	-	24	2/1.3	8,000	ATB	C1a	1	1	3165140373678	2 608 641 185

190	30	-	-	48	2/1.3	8,000	ATB	C1a	1	1	3165140373685	2 608 641 186
190	30	-	-	12	2.6/1.6	8,000	ATB	C1a	1	1	3165140373692	2 608 641 187
190	30	-	-	60	2.6/1.6	8,000	ATB	C1a	1	1	3165140373708	2 608 641 188
200	30	-	-	24	2.8/1.8	7,500	ATB	C1a	1	1	3165140194129	2 608 640 618
200	30	-	-	48	2.8/1.8	7,500	ATB	C1a	1	1	3165140194143	2 608 640 620
210	30	-	-	24	2.8/1.8	7,500	ATB	C1a	1	1	3165140194150	2 608 640 621
210	30	-	-	36	2.8/1.8	7,000	ATB	C1a	1	1	3165140194167	2 608 640 622
210	30	-	-	48	2.8/1.8	7,500	ATB	C1a	1	1	3165140194174	2 608 640 623
210	30	-	-	30	2.4/1.8	7,000	ATB/FT	C1a	1	1	3165140240147	2 608 640 803
210	30	-	-	60	2.8/1.8	7,500	ATB	C1a	1	1	3165140373722	2 608 641 190
230	30	-	-	24	2.8/1.8	6,500	ATB	C1a	1	1	3165140194211	2 608 640 627
230	30	-	-	36	2.8/1.8	6,500	ATB	C1a	1	1	3165140195157	2 608 640 628
230	30	-	-	48	2.8/1.8	6,500	ATB	C1a	1	1	3165140194228	2 608 640 629
230	30	-	-	18	2.4/1.8	6,500	ATB/FT	C1a	1	1	3165140240154	2 608 640 804
230	30	-	-	30	2.4/1.8	6,500	ATB/FT	C1a	1	1	3165140240161	2 608 640 805
235	30	25	-	24	2.8/1.8	6,500	ATB	C1a	1	1	3165140194990	2 608 640 725
235	30	25	-	48	2.8/1.8	6,500	ATB	C1a	1	1	3165140195010	2 608 640 727
235	30	25	-	30	2.4/1.8	6,000	ATB/FT	C1a	1	1	3165140240185	2 608 640 807
235	30	25	-	60	2.8/1.8	6,500	ATB	C1a	1	1	3165140373746	2 608 641 192
250	30	-	-	40	3.2/2.2	6,000	ATB	C1a	1	1	3165140195027	2 608 640 728
250	30	-	-	60	3.2/2.2	6,000	ATB	C1a	1	1	3165140195034	2 608 640 729