

**COMBI CHECK Volt Testers****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE-Norm 0682, section 401
- high peak voltage strength
- the right tester for every application

**General ordering data**

|            |                                               |
|------------|-----------------------------------------------|
| Order No.  | 9918860000 (14mm tips); 9204230000 (2mm tips) |
| Type       | COMBI CHECK                                   |
| Version    | 2-pole voltage tester                         |
| GTIN (EAN) | 4032248405749                                 |
| Qty.       | 1 pc(s).                                      |

## Passeinsatz für Einsätze E14 4 A COMBI CHECK

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-2083  
www.weidmueller.com

## Technical data

### Dimensions

|        |       |
|--------|-------|
| Weight | 290 g |
|--------|-------|

### Technical data

|         |                |
|---------|----------------|
| Version | Protective bag |
|---------|----------------|

### Product data

|                            |                                       |                                  |                                                |
|----------------------------|---------------------------------------|----------------------------------|------------------------------------------------|
| AC voltage measuring range | 6-690 V                               | Frequency range, min.            | 0 Hz                                           |
| Frequency range, max.      | 100 Hz                                | Protection degree                | IP 65                                          |
| Battery type               | 1.5 V type AAA battery                | Tested and approved according to | EN/IEC 61243-3 :2010-10<br>(VDE 0682 part 401) |
| Peak voltage resistance    | 8 kV                                  | Display                          | LED                                            |
| DC voltage display         | 6,12, 24, 50, 120, 230, 400,<br>690 V | AC voltage display               | 6,12, 24, 50, 120, 230, 400,<br>690 V          |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 2.0   | EC000494    | ETIM 3.0   | EC000494    |
| UNSPSC     | 41-11-36-37 | eClass 4.1 | 27-20-03-08 |
| eClass 5.1 | 27-20-03-08 | eClass 6.0 | 27-20-03-08 |
| eClass 7.0 | 27-20-03-08 |            |             |

### Product information

|                        |                                                                                                                                              |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Description of article | Voltage tester up to 690 V/ 100 Hz LED                                                                                                       |
| Product description    | <ul style="list-style-type: none"> <li>• Phase sequence indicator</li> <li>• Single-pole phase test</li> <li>• Batteries included</li> </ul> |

### Approvals

|           |
|-----------|
| Approvals |
|-----------|

**Passeinsatz für Einsätze E14 4 A  
COMBI CHECK**

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-2083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

