

# KERN EOA 100K-2

Paketwaage für einfaches und schnelles Wiegen im Büro, Produktion, Versand etc.



## Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	515 x 388 x 137 mm
Gross weight:	4,450 kg
Net weight:	3,750 kg
Shipping method:	Parcel service

## Construction

Cable length of display device:	1,400 m
Casing material:	plastic
Dimensions of display device (WxDxH):	225 x 110 x 45 mm
Dimensions of weighing plate (WxDxH):	315 x 305 x 55 mm
Material weighing plate:	Steel lacquered
Weighing surface (WxD):	315 x 305 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	250 g
Readout [d]:	50 g
Recommended adjusting weight:	100 kg (M1)
Reproducibility:	50 g
Resolution:	3000
Stabilisation time:	3 s
Tare range:	150 kg
Warm up time:	10 min
Weighing range [Max]:	150 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	2,500 cm
-----------------------	----------

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	220 V - 240 V AC 50 Hz
----------------	------------------------

n/a: Mains adapter external

## Power supply

Operating time:	60 h
-----------------	------

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129