

SITOP PSU100S 24 V/5 A  
 SITOP PSU100S 24 V/5 A Stabilized power supply input: 120/230 V  
 AC, output: 24 V DC/5 A



Input	
Input	1-phase AC
Supply voltage	
<ul style="list-style-type: none"> <li>• 1 at AC Rated value</li> <li>• 2 at AC Rated value</li> <li>• Note</li> </ul>	120 V 230 V Automatic range selection
Input voltage	
<ul style="list-style-type: none"> <li>• 1 at AC</li> <li>• 2 at AC</li> </ul>	85 ... 132 V 170 ... 264 V
Wide-range input	No
Overvoltage resistance	2.3 × Vin rated, 1.3 ms
Mains buffering at lout rated, min.	20 ms; at Vin = 93/187 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 ... 63 Hz
Input current	
<ul style="list-style-type: none"> <li>• at rated input voltage 120 V</li> <li>• at rated input voltage 230 V</li> </ul>	2.34 A 1.36 A
Switch-on current limiting (+25 °C), max.	40 A

I <sup>2</sup> t, max.	1 A <sup>2</sup> ·s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C

## Output

Output	Controlled, isolated DC voltage
Rated voltage V <sub>out</sub> DC	24 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	1 %
Residual ripple peak-peak, max.	150 mV
Residual ripple peak-peak, typ.	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	140 mV
Adjustment range	22.8 ... 28 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	Overshoot of V <sub>out</sub> < 3 %
Startup delay, max.	0.3 s
Voltage rise, typ.	15 ms
Rated current value I <sub>out</sub> rated	5 A
Current range	0 ... 6 A
• Note	6 A up to +45°C; +60 ... +70 °C: Derating 1.6%/K
Supplied active power typical	144 W
Short-term overload current	
• on short-circuiting during the start-up typical	18 A
• at short-circuit during operation typical	18 A
Duration of overloading capability for excess current	
• on short-circuiting during the start-up	800 ms
• at short-circuit during operation	800 ms
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

## Efficiency

Efficiency at V <sub>out</sub> rated, I <sub>out</sub> rated, approx.	88 %
Power loss at V <sub>out</sub> rated, I <sub>out</sub> rated, approx.	16 W

## Closed-loop control

Dynamic mains compensation (V <sub>in</sub> rated ±15 %), max.	0.3 %
Dynamic load smoothing (I <sub>out</sub> : 10/90/10 %), U <sub>out</sub> ± typ.	3 %

Load step setting time 10 to 90%, typ.	1 ms
Load step setting time 90 to 10%, typ.	1 ms
<b>Protection and monitoring</b>	
Output overvoltage protection	protection against overvoltage in case of internal fault $V_{out} < 33 \text{ V}$
Current limitation	6 ... 7.1 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Constant current characteristic
Enduring short circuit current RMS value	7.1 A
• typical	
Overcurrent overload capability in normal operation	overload capability 150 % $I_{out}$ rated up to 5 s/min
Overload/short-circuit indicator	-
<b>Safety</b>	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage $U_{out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current	3.5 mA
• maximum	
• typical	0.4 mA
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-
CB approval	Yes
Marine approval	BV, DNV GL
Degree of protection (EN 60529)	IP20
<b>EMC</b>	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2
<b>Operating data</b>	
Ambient temperature	-25 ... +70 °C with natural convection
• during operation	
— Note	
• during transport	
• during storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
<b>Mechanics</b>	

Connection technology	screw-type terminals
Connections <ul style="list-style-type: none"> <li>• Supply input</li> <li>• Output</li> <li>• Auxiliary</li> </ul>	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm <sup>2</sup> single-core/finely stranded +, -: 2 screw terminals each for 0.5 ... 2.5 mm <sup>2</sup> Alarm signals: 2 screw terminals for 0.5 ... 2.5 mm <sup>2</sup>
Connections signaling contact	2 screw terminals for 0.5 ... 2.5 mm <sup>2</sup>
Width of the enclosure	50 mm
Height of the enclosure	125 mm
Depth of the enclosure	120 mm
Required spacing <ul style="list-style-type: none"> <li>• top</li> <li>• bottom</li> <li>• left</li> <li>• right</li> </ul>	50 mm 50 mm 0 mm 0 mm
Weight, approx.	0.5 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Buffer module
Mechanical accessories	Device identification label 20 mm × 7 mm, pale turquoise 3RT1900-1SB20
MTBF at 40 °C	1 998 441 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)